

Specifications

Eaton S10N04P01P

Eaton General-Purpose Encapsulated Transformer, EP, Single-phase, PV: 120 X 240V, Taps: None, SV: 12/24V, 115°C, 1 kVA, Al windings, Frame: 67P, Indoor-Outdoor.



Photo is representative



General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton General purpose encapsulated transformer |
| CATALOG NUMBER | S10N04P01P |
| UPC | 786680072703 |
| PRODUCT LENGTH/DEPTH | 6.56 in |
| PRODUCT HEIGHT | 13.03 in |
| PRODUCT WIDTH | 5.53 in |
| PRODUCT WEIGHT | 26 lb |
| WARRANTY | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| CERTIFICATIONS | UL Listed |



Powering Business Worldwide

Physical Attributes

| | |
|-------------------|--|
| COIL MATERIAL | Aluminum |
| DESIGN | EP |
| ENCLOSURE | NEMA 3R |
| FRAME | 67P |
| TAP SIZE | None |
| TYPE | General-Purpose Encapsulated Transformer |
| WIRING CONNECTION | 3B |

Miscellaneous

| | |
|---------------|----------------|
| WEATHERSHIELD | Indoor-Outdoor |
|---------------|----------------|

Performance Ratings

| | |
|--------------------|--------------|
| FREQUENCY RATING | 60 Hz |
| KVA RATING | 1 kVA |
| PHASE | Single-phase |
| PRIMARY VOLTAGE | 120 V, 240 V |
| SECONDARY VOLTAGE | 12/24 V |
| TEMPERATURE RISE | 115 °C rise |
| VOLT AMPERE RATING | 1 kVA |

Resources

| | |
|-------------------------------|--|
| CATALOGS | Commercial Distribution, Transformers, Volume 2, Tab 2 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - S10N04P01P |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

