

Specifications

Photo is representative

Eaton S10N04P01P

Eaton General-Purpose Encapsulated Transformer, EP, Single-phase, PV: 120 X 240V, Taps: None, SV: 12/24V, 115°C, 1 kVA, Al windings, Frame: 67P, Indoor-Outdoor.

General specifications

PRODUCT NAME	Eaton General purpose encapsulated transformer
CATALOG NUMBER	S10N04P01P
UPC	786680072703
PRODUCT LENGTH/DEPTH	6.56 in
PRODUCT HEIGHT	13.03 in
PRODUCT WIDTH	5.53 in
PRODUCT WEIGHT	26 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Physical Attributes	
COIL MATERIAL	Aluminum
DESIGN	EP
ENCLOSURE	NEMA 3R
FRAME	67P
TAP SIZE	None
TYPE	General-Purpose Encapsulated Transformer
WIRING CONNECTION	3B

Miscellaneous	
WEATHERSHIELD	Indoor-Outdoor

Performance Ratings	
FREQUENCY RATING	60 Hz
KVA RATING	1 kVA
PHASE	Single-phase
PRIMARY VOLTAGE	120 V, 240 V
SECONDARY VOLTAGE	12/24 V
TEMPERATURE RISE	115 °C rise
VOLT AMPERE RATING	1 kVA

Resources	
CATALOGS	Commercial Distribution, Transformers, Volume 2, Tab 2
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - S10N04P01P

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

