

Specifications

Photo is representative

Eaton S10N06A82N

Eaton General purpose encapsulated transformer, buck-boost general-purpose encapsulated transformer, EP, aluminum, NEMA 3R, 54, 60 Hz, single-phase, 120 V, 240 V, 16/32 V, NONE, 115 °C rise, 0.1 KVA, indoor-outdoor, 3C

General specifications

PRODUCT NAME	Eaton General purpose encapsulated transformer
CATALOG NUMBER	S10N06A82N
UPC	786680383168
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	8.91 in
PRODUCT WIDTH	4.11 in
PRODUCT WEIGHT	8 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed
CATALOG NOTES	Model N

Physical Attributes	
COIL MATERIAL	Aluminum
DESIGN	EP
ENCLOSURE	NEMA 3R
FRAME	54
TAP SIZE	None
TYPE	Buck-Boost General-Purpose Encapsulated Transformer
WIRING CONNECTION	3C

Miscellaneous	
WEATHERSHIELD	Indoor-Outdoor

Performance Ratings	
FREQUENCY RATING	60 Hz
PHASE	Single-phase
PRIMARY VOLTAGE	120 V, 240 V
SECONDARY VOLTAGE	16/32 V
TEMPERATURE RISE	115 °C rise
VOLT AMPERE RATING	0.1 kVA

Resources	
CATALOGS	Commercial Distribution, Transformers, Volume 2, Tab 2
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - S10N06A82N
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

Follow us on social media to get the latest product and support information.

