

# Eaton S10N06P76P

Catalog Number: S10N06P76P

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 58AP, 60 Hz, single-phase, 120 V, 240 V, 16/32 V, NONE, 115 °C rise, 0.75 KVA, indoor-outdoor, 3C

## General specifications



Photo is representative

|  |                       |
|--|-----------------------|
| <b>Product Name</b>  | <b>Catalog Number</b> |
| Eaton General purpose encapsulated transformer   | S10N06P76P            |
|  | UPC                   |
|  | 786680073663          |
| <b>Product Length/Depth</b>  | <b>Product Height</b> |
| 5.99 in  | 11.68 in              |
| <b>Product Width</b>   | <b>Product Weight</b> |
| 4.99 in  | 21 lb                 |
| <b>Warranty</b>  | <b>Certifications</b> |
| Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |                       |

## Physical Attributes

### Coil material

Aluminum

### Design

EP

### Enclosure

NEMA 3R

### Frame

58AP

### Tap size

None

### Type

General-Purpose Encapsulated Transformer

### Wiring connection

3C

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

120 V, 240 V

### Secondary Voltage

16/32 V

### Temperature rise

115 °C rise

### Volt ampere rating

0.75 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

Commercial Distribution, Transformers, Volume 2, Tab 2

### Specifications and datasheets

Eaton Specification Sheet - S10N06P76P

### Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton S10N06P76P

Catalog Number: S10N06P76P

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 58AP, 60 Hz, single-phase, 120 V, 240 V, 16/32 V, NONE, 115 °C rise, 0.75 KVA, indoor-outdoor, 3C

## General specifications



Photo is representative

|  |                       |
|--|-----------------------|
| <b>Product Name</b>  | <b>Catalog Number</b> |
| Eaton General purpose encapsulated transformer   | S10N06P76P            |
|  | UPC                   |
|  | 786680073663          |
| <b>Product Length/Depth</b>  | <b>Product Height</b> |
| 5.99 in  | 11.68 in              |
| <b>Product Width</b>   | <b>Product Weight</b> |
| 4.99 in  | 21 lb                 |
| <b>Warranty</b>  | <b>Certifications</b> |
| Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |                       |

## Physical Attributes

### Coil material

Aluminum

### Design

EP

### Enclosure

NEMA 3R

### Frame

58AP

### Tap size

None

### Type

General-Purpose Encapsulated Transformer

### Wiring connection

3C

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

120 V, 240 V

### Secondary Voltage

16/32 V

### Temperature rise

115 °C rise

### Volt ampere rating

0.75 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

Commercial Distribution, Transformers, Volume 2, Tab 2

### Specifications and datasheets

Eaton Specification Sheet - S10N06P76P

### Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)