



S1931

LU100
100 watt; High Pressure Sodium HID; Mogul base; ET23 1/2;
Clear; 22 CRI; 2100K

Features

- High Efficacy
- Long Life
- Universal operating position



S1931

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	ANSI Code	Lamp Code
S1931	045923019319	100	ET23.5	Mogul	E39	S54	LU100
Finish	MOL In Inches	MOD In Inches	Average Rated Hours	Initial Lumens	Kelvin Temp	Pack	CRI
Clear	7 3/4"	2.94"	24000	24000	2100	12	22
Burning Position				RoHS Compliant			
Universal				Yes			



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

