



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## S202K16 2P 480V 16A Breaker

*Industrial Connections &*

Catalog Number	S202K16
Manufacturer	Industrial Connections &
Description	Miniature Circuit Breaker, 16 A, Thermal Magnetic Tripping Mechanism, Screw Terminal, Din Rail Mount, 277/Y480 V Ac;60/110 V DC, 50/60 HZ, +55 °C Operating Temperature, -25 °C Operating Temperature, 88 MM Overall Height, 69 MM Overall Length, 35 MM Overall Width, 0.57 LB
Weight per unit	0.5700 (lbs/each)
Product Category	2 Pole Supplementary Protector

### Features

amperage rating	16 lbs./100ft
Poles	2 in
Trip Type	OUTSIDE CORNER FITTING, OUTSIDE CORNER FITTING TYPE; ABS PLASTIC MATERIAL; 1.5 INCH L X 0.91 INCH W X 0.6 INCH H SIZE; WHITE FINISH; PAN-WAY LD10 SERIES NON-METALLIC SURFACE RACEWAY USED ON; UL, CE APPROVAL; 10 STANDARD PACKAGE; PAN-WAY[R] BRAND

### Dimensions and Weight

Height	88 Millimeters
Length	69 Millimeters
Width	35 W

### Descriptions

Description	2P 480V 16A BREAKER
extra long description	ABB S202-K16 LEGACY SEE REPLACEMENT
Special Features	High performance MCB provides compact supplementary, energy limiting, circuit protection

### Manufacturer Information

GTIN	00662019170923
sub brand	System pro M compact
UPC	662019170923

### Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	High Performance MCB Provides Compact Supplementary, Energy Limiting, Circuit Protection

### Availability

Status	Inactive
--------	----------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	5
Weight Per each	0.57

## Uses, Certifications, and Standards

Application	For use as a supplemental protection device
Operating Temperature	-25 to +55 Degrees Celcius
standard	UL 1077, CSA 22.2 No. 235, IEC 60898