



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S29558 9.5W Led A19 40K Non-Dim 800LM 4-Pack

Satco

Catalog Number	S29558
Manufacturer	Satco
Description	9.5W A19 Led Lamp Frosted 40K E26 220' Beam 120V Non-Dimmable 4-PK
Weight per unit	0.5500 (lbs/each)
Product Category	Led A-Line A Shape Lamps

Features

average life	15000
Base	Medium
beam angle	220
dimmable	No
lumens	800
Shape	A19
Voltage Rating	120
Warranty	3 Year Limited - 10 hr per day
Wattage	10

Material, Color, and Finish

color temperature	4000
-------------------	------

Dimensions and Weight

Diameter	2.38
Length	4.38

Descriptions

Description	9.5W LED A19 40K NON-DIM 800LM 4-PACK
extra long description	SATCO S29558 9.5A19/LED/40K/ND/120V
Long Description	9.5W A19 LED Lamp Frosted 40K E26 220' Beam 120V Non-Dimmable 4-PK
Product Type	9.5A19/Led/40K/ND/120V/4PK
Special Features	Enclosed fixture rated: Yes ; Operating Temp: -20C (-4F) to a maximum of +45C (+113F) ; Energy Star rated: Yes ; Lamp appearance: Frosted White ; Incandescent equivalent: 60 watts

Manufacturer Information

Brand	Satco
GTIN	00045923295584
Manufacturers Part Number	S29558
UPC	045923295584



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
Type	Type A

Packaging

Carton	1
Package	12
Weight Per each	0.55

Uses, Certifications, and Standards

Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)
-----------------------	--