

Project Name

Location

Prepared By



SATCO S29867

4W CFC/LED/50K/CL/120V

Notes

(www) 02-24-2023 09:53:21

General

| | |
|-------------------------|---------------|
| Status | Discontinued |
| Substitute | S21299 |
| Watts | 4W |
| Incandescent Equivalent | 40W |
| Volts | 120V |
| Shape | CA11 |
| Base | Candelabra |
| ANSI Base | E12 |
| Finish | Clear |
| CCT (Kelvin) | 5000K |
| Temperature | Natural Light |
| CRI | 80+ |
| Lumens | 350L |
| Beam Spread | 360 |
| Dimmable | Yes-Dimmable |
| Hours Rated | 15000 |
| Product Category | Candle |
| Technology | LED |

Electrical

| | |
|-----------------------|----------------------------|
| Operating Frequency | 60Hz |
| Power Factor | 0.9 |
| Operating Position | Universal |
| Operating Temperature | -20C (-4F) to +45C (+113F) |

Physical

| | |
|--------------|------|
| MOL | 4.69 |
| MOD | 1.38 |
| Weight (lb.) | 0.03 |

Additional Information

| | |
|----------------------------|----------------|
| Rated For Enclosed Fixture | Yes |
| Warranty | 3 Year Limited |

Compliance

| | |
|----------------------|-----------------|
| Safety Listing | cULus |
| Location Rating | Damp |
| California Status | Non-Compliant |
| Title 20 / 24 Status | Non-Compliant |
| Colorado Status | Lawful for sale |
| Hawaii Status | Lawful for sale |
| Nevada Status | Lawful for sale |
| Vermont Status | Lawful for sale |
| Washington Status | Lawful for sale |
| RoHS Compliant | Yes |
| FCC Compliant | Yes |
| SDS Sheet | LED_Lamp |