

S2-B


Socket for 8-pin Relays and Time Cubes

Rated Load	10 A / 300 V
Specifications	
Rated impulse withstand voltage	2.5 kV rms / 1 min
– All terminals / DIN rail	2.5 kV rms / 1 min
– Terminal / Terminal	
Cross-section of connecting wire	
– Single-wire	4 mm² / AWG 12 or 2 x 2.5 mm² / AWG 14
– Multi-wire	0.34 mm² / AWG 22 - 2.5 mm² / AWG 14
Nominal screw torque	0.7 Nm
Screw dimensions	M3 Pozi slot
Mounting	TS-35 or Back Panel Mounting
Ambient temperature operation / storage	-40...60 °C / -40 ... 80 °C (no ice)
Weight	48g


Included Accessories	
Retaining Clip, plastic	S30-CM for C2 / C2x Relays
Optional Accessories	
Retaining clip, steel	HF-32 (BAG 10 PCS) for C2 / C2x Relays HF-33 (BAG 10 PCS) for Time Cube CTx



Connection diagram



Dimensions [mm]



Technical approvals, conformities



S2-B


Socket for 8-pin Relays and Time Cubes

Rated Load	10 A / 300 V
Specifications	
Rated impulse withstand voltage	2.5 kV rms / 1 min
– All terminals / DIN rail	2.5 kV rms / 1 min
– Terminal / Terminal	
Cross-section of connecting wire	
– Single-wire	4 mm² / AWG 12 or 2 x 2.5 mm² / AWG 14
– Multi-wire	0.34 mm² / AWG 22 - 2.5 mm² / AWG 14
Nominal screw torque	0.7 Nm
Screw dimensions	M3 Pozi slot
Mounting	TS-35 or Back Panel Mounting
Ambient temperature operation / storage	-40...60 °C / -40 ... 80 °C (no ice)
Weight	48g


Included Accessories	
Retaining Clip, plastic	S30-CM for C2 / C2x Relays
Optional Accessories	
Retaining clip, steel	HF-32 (BAG 10 PCS) for C2 / C2x Relays HF-33 (BAG 10 PCS) for Time Cube CTx



Connection diagram



Dimensions [mm]



Technical approvals, conformities

