



S3105

500T3Q/CL
500 watt; Halogen; T3; Clear; 1500 Average rated Hours; 9500 Lumens; Double Ended base; 120 volts



Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output

S3105

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | Voltage |
|-------------|---------------|----------------|------------|----------------|-------------|------------|---------------------|
| S3105 | 045923031052 | 500 | T3 | Double Ended | R7s | 500T3Q/CL | 120 |
| Finish | MOL In Inches | MOD In Inches | Filament | Initial Lumens | Kelvin Temp | Color | Average Rated Hours |
| Clear | 4 11/16" | 0.38" | C-8 | 9500 | 2900 | Warm White | 1500 |
| Pack | Package Type | RoHS Compliant | | | | | |
| 480/12 | Box | Yes | | | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S3105

500T3Q/CL
500 watt; Halogen; T3; Clear; 1500 Average rated Hours; 9500 Lumens; Double Ended base; 120 volts



Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output

S3105

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | Voltage |
|-------------|---------------|----------------|------------|----------------|-------------|------------|---------------------|
| S3105 | 045923031052 | 500 | T3 | Double Ended | R7s | 500T3Q/CL | 120 |
| Finish | MOL In Inches | MOD In Inches | Filament | Initial Lumens | Kelvin Temp | Color | Average Rated Hours |
| Clear | 4 11/16" | 0.38" | C-8 | 9500 | 2900 | Warm White | 1500 |
| Pack | Package Type | RoHS Compliant | | | | | |
| 480/12 | Box | Yes | | | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

