



Pass and Seymour  
**2-Gang Chrome Wall Plate, 1 Power Outlet Receptacle Opening**  
Part No. S3863C



TwoGang Power Outlet Receptacle Opening, 2.4688 hole for 2.375 diameter device -4 mtg. holes, Smooth Metal.

## Features & Benefits

Chrome: .040" thick.

Lacquered to prevent corrosion.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Variety of special plated finishes.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

70% copper, 30% zinc alloy gives warm, appealing finish to modern decor as well as retrofit applications.

Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.

Packaged in protective film, with finish-matching screws.

Paintable to match plastic plates.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Chrome
Finish	Metallic	UPC Number	785007138276
Country Of Origin	United States	Wall Plate Size	Standard Size
Wall Plate Type	Outlet, Round	Application Sector	Commercial, Residential
Warranty Type	1-Year Limited Warranty	Type	Wall Plate

### Dimensions

---

Product Width US	4.56 in	Product Depth US	0.2 in
------------------	---------	------------------	--------

---

Product Height US	4.5 in
-------------------	--------

---

### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

### Additional Information

---

Product Environmental Profile	Yes
-------------------------------	-----

---

### Technical Information

---

Thickness	0.04 in	Number of Gangs	2
-----------	---------	-----------------	---

---

Indoor/Outdoor	Indoor	Mounting Type	Strap Mounted
----------------	--------	---------------	---------------

---

Orientation	Vertical
-------------	----------

---