



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## S41010CT00 1" SS304 Rigid Conduit, 10' W/Coupling

Calbrite

Catalog Number	S41010CT00
Manufacturer	Calbrite
Description	Rigid Stainless Steel 304 Conduit With Coupling 1" Trade Size 10 Feet Long
Weight per unit	16.1 (lbs/each)
Product Category	Galvanized Heavy Wall Conduit

### Features

Inside Diameter	1.05
Material	Stainless Steel - 304L
outside diameter	1.315
Wall Thickness	0.132

### Material, Color, and Finish

Color	Polished Silver
Finish	#4 Polished Finish

### Dimensions and Weight

Length	120
--------	-----

### Descriptions

Description	1" SS304 RIGID CONDUIT, 10' W/COUPLING
extra long description	CAL S41010CT00 1" X 10' SS304 CONDU
Features	Stainless conduit is specified in corrosive applications that exceed the limitations of aluminum, fiberglass, rigid steel, PVC, and PVC coated conduit. Type 304 and 316 UL-listed stainless steel conduit meets and exceeds current requirements for wash down and harsh/corrosive environments and satisfies the strictest mandates for plant cleanliness by various state agencies and hundreds of common regulatory requirements.
Long Description	Rigid Stainless Steel 304 Conduit With Coupling 1" Trade Size 10 Feet Long
Product Type	1" X 10' SS304 Conduit W/ Coupling
Short Description	SS_RGD_304

### Manufacturer Information

Brand	CALBRITE
GTIN	00847656000035
Manufacturers Part Number	S41010CT00
UPC	847656000035



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... Stainless Rigid Conduit  
Type ..... RIGID

## Trade Size

Trade Size ..... 1

## Availability

minimum qty ..... 10

## Packaging

Carton ..... 10

Package ..... 50

Weight ..... 1.61

Weight Per foot ..... 16.1

## Uses, Certifications, and Standards

Temperature Rating ..... 1600