



# S5858

MP100/ED17/U/PS  
100 watt; Metal Halide HID; Medium base; ED17; Clear; 65  
CRI; 4000K

### Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Pulse Start
- Open Rated



S5858

| Item Number | UPC           | Watts         | Lamp Shape          | Base             | ANSI Base      | ANSI Code  | Lamp Code       |
|-------------|---------------|---------------|---------------------|------------------|----------------|------------|-----------------|
| S5858       | 045923058585  | 100           | ED17                | Medium           | E26            | M90/O      | MP100/ED17/U/PS |
| Finish      | MOL In Inches | MOD In Inches | Average Rated Hours | Initial Lumens   | Kelvin Temp    | Color      | Pulse Start     |
| Clear       | 5.44"         | 2.13"         | 10000               | 9500             | 4000           | Cool White | Yes             |
| Open Rated  | Pack          | Package Type  | CRI                 | Burning Position | RoHS Compliant |            |                 |
| Yes         | 12            | Box           | 65                  | Universal        | Yes            |            |                 |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S5858

MP100/ED17/U/PS  
100 watt; Metal Halide HID; Medium base; ED17; Clear; 65  
CRI; 4000K

### Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Pulse Start
- Open Rated



S5858

| Item Number | UPC           | Watts         | Lamp Shape          | Base             | ANSI Base      | ANSI Code  | Lamp Code       |
|-------------|---------------|---------------|---------------------|------------------|----------------|------------|-----------------|
| S5858       | 045923058585  | 100           | ED17                | Medium           | E26            | M90/O      | MP100/ED17/U/PS |
| Finish      | MOL In Inches | MOD In Inches | Average Rated Hours | Initial Lumens   | Kelvin Temp    | Color      | Pulse Start     |
| Clear       | 5.44"         | 2.13"         | 10000               | 9500             | 4000           | Cool White | Yes             |
| Open Rated  | Pack          | Package Type  | CRI                 | Burning Position | RoHS Compliant |            |                 |
| Yes         | 12            | Box           | 65                  | Universal        | Yes            |            |                 |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

