



# S5878

MS400/ED28 /PS /U /4K  
400 watt; Metal Halide HID; Mogul base; ED28; Clear; 65 CRI;  
4200K

### Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Pulse Start



S5878

| Item Number | UPC          | Watts | Lamp Shape | Base  | ANSI Base | ANSI Code | Lamp Code             |
|-------------|--------------|-------|------------|-------|-----------|-----------|-----------------------|
| S5878       | 045923058783 | 400   | ED28       | Mogul | E39       | M155/E    | MS400/ED28 /PS /U /4K |

| Finish | MOL In Inches | MOD In Inches | Average Rated Hours | Initial Lumens | Kelvin Temp | Color      | Pulse Start |
|--------|---------------|---------------|---------------------|----------------|-------------|------------|-------------|
| Clear  | 8.31"         | 3.56"         | 20000               | 44000          | 4200        | Cool White | Yes         |

| Pack | Package Type | CRI | Burning Position | RoHS Compliant |
|------|--------------|-----|------------------|----------------|
| 12   | Box          | 65  | Universal        | Yes            |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S5878

MS400/ED28 /PS /U /4K  
400 watt; Metal Halide HID; Mogul base; ED28; Clear; 65 CRI;  
4200K

### Features

- Uniform light distribution
- Superior performance
- High Efficiency
- Pulse Start



S5878

| Item Number | UPC           | Watts         | Lamp Shape          | Base           | ANSI Base   | ANSI Code  | Lamp Code             |
|-------------|---------------|---------------|---------------------|----------------|-------------|------------|-----------------------|
| S5878       | 045923058783  | 400           | ED28                | Mogul          | E39         | M155/E     | MS400/ED28 /PS /U /4K |
| Finish      | MOL In Inches | MOD In Inches | Average Rated Hours | Initial Lumens | Kelvin Temp | Color      | Pulse Start           |
| Clear       | 8.31"         | 3.56"         | 20000               | 44000          | 4200        | Cool White | Yes                   |
| Pack        | Package Type  | CRI           | Burning Position    | RoHS Compliant |             |            |                       |
| 12          | Box           | 65            | Universal           | Yes            |             |            |                       |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

