



Shown actual size: Skylark® preset dimmer and 1-gang Claro® wallplate in almond (AL)

SKYLARK® dimmers

product family features

- rocker switch returns light to your favorite light level
- slide up to brighten, down to dim (adjust light to suit any activity)
- coordinating Claro® wallplates available separately (including stainless steel)
- **eco-dim**® model available

available models

source type

- incandescent/halogen lighting
- magnetic low-voltage lighting
- electronic low-voltage lighting
- fluorescent lighting
- LED lighting
- dimmable compact fluorescent
- quiet 3-speed fan controls
- quiet 3-speed fan/light controls
- fully variable fan controls

control locations

- single pole (one location)
- 3-way (two locations)

available colors (see page 12 for color swatches)

colors (gloss finish)

- | | |
|------------------------|-----------------|
| WH white | GR gray |
| IV ivory | BR brown |
| AL almond | BL black |
| LA light almond | |

Questions on installation or selection?
Call Lutron® 24 hours/7 days a week at
1.800.523.9466 or visit www.lutron.com

dimmers with on/off switch



- rocker switch turns on/off
- slide up to brighten, down to dim
- eco-dim® model guarantees at least 15% energy savings compared to a standard switch

incandescent/halogen

single pole	600W	S-600P-
single pole	1000W	S-10P-
3-way	600W	S-603P-
3-way	1000W	S-103P-

incandescent/halogen — eco-dim®† NEW

single pole/3-way	600W	S-603PG-
-------------------	------	-----------------

magnetic low-voltage

single pole	600 VA (450 W)	SLV-600P-
3-way	600 VA (450 W)	SLV-603P-

Suggested maximum lighting load for magnetic low-voltage dimming is 450W for 600VA products to allow for transformer losses.

electronic low-voltage*

single pole	300W	SELV-300P-
3-way	300W	SELV-303P-

* requires neutral wire connection

† available in white, ivory, almond, and light almond

dimmers with on/off switch & locator light



- rocker switch turns on/off
- slide up to brighten, down to dim
- includes locator light

incandescent/halogen

single pole	600W	S-600PNL-
single pole	1000W	S-10PNL-
3-way	600W	S-603PNL-
3-way	1000W	S-103PNL-

slide-to-off dimmers



- slide up to on/brighten, down to dim/off

incandescent/halogen

single pole	600W	S-600-
single pole	1000W	S-1000-

See page 77 for available colors.

To order, add color suffix to model number.

Example: **S-600P- WH**

fluorescent dimming with Hi-lume®, Compact SE™, Eco-10®, EcoSystem® ballasts, and Hi-lume® LED



- use with Lutron® 3-wire line-voltage control electronic dimming ballasts
- please refer to the Lutron® Fluorescent Dimming Systems Selection Guide (P/N 366-002) for more information
- no derating if ganged

fluorescent*

single pole	120V	8A	SF-10P-
single pole	277V	6A	SF-12P-277-
3-way	120V	8A	SF-103P-
3-way	277V	6A	SF-12P-277-3-

LED (with Hi-lume® LED driver only)* **NEW**

single pole	120V	8A	SF-10P-
single pole	277V	6A	SF-12P-277-
3-way	120V	8A	SF-103P-
3-way	277V	6A	SF-12P-277-3-

LED (with GRX-TVI 0-10 VDC sink control)* **NEW**

single pole	16A load 30 mA control 120/277V	SF-10P-
3-way	16A load 30 mA control 120/277V	SF-103P-

* requires neutral wire connection

fluorescent dimming with Tu-Wire® ballasts



- use with Lutron® Tu-Wire® line-voltage control electronic dimming ballasts
- for information on using Lutron® dimmers to control Advance® Mark 10® dimming ballasts, visit the Lutron® website at www.lutron.com/advance
- must be derated if ganged

fluorescent Tu-Wire®

single pole/3-way 5A **SFTU-5A3P-**

compact fluorescent dimming with Philips® DIMMABLE Energy Saver CFL **NEW**



- use **only** with **PHILIPS®** models:
EL/A
R30 DIM
R40 DIM
PAR38 DIM
- includes locator light
- no derating if ganged
- always turn on, regardless of slider setting
- isolates bulb from unstable line voltage

screw base dimmable compact fluorescent

single pole/3-way 200W **SPDC-203P-**

Standard incandescent/halogen dimmers are not UL listed for screw base dimmable compact fluorescent (CFL) lamps.

See page 77 for available colors.

To order, add color suffix to model number.

Example: **SF-10P- WH**

slide-to-off fan control & on/off light switch



- fan control** (top)
- slide up to on/increase fan speed, down to decrease/off
 - 3 quiet fan speeds for increased comfort
 - for use with only one ceiling paddle fan

- switch** (bottom)
- rocker switch turns light on/off

quiet 3-speed control & switch

single pole fan control 1.5A (top) **SFSQ-LF-**
single pole switch 360W (bottom)
(incandescent/halogen loads only)

slide-to-off fan control



- slide up to on/increase speed, down to decrease/off
- must be derated if ganged

quiet 3-speed control

single pole fan control 1.5A **SFSQ-F-**
2.0A **SFSQ-F-HO-**

for use with only one ceiling paddle fan

fully variable control

single pole fan control 5A **SFS-5E-**
for use with multiple ceiling paddle fans or exhaust fans

See page 77 for available colors.
To order, add color suffix to model number.
Example: **SFSQ-LF- WH**

dual slide-to-off dimmers (two loads)



- dimmers** (left/right)
- slide up to on/brighten, down to dim/off

incandescent/halogen

single pole dimmer 300W light (left) **S2-L-**
single pole dimmer 300W light (right)

dual slide-to-off fan control & dimmer



- fan control** (left)
- slide up to on/increase speed, down to decrease/off
 - 3 quiet fan speeds for increased comfort
- dimmer** (right)
- slide up to on/brighten, down to dim/off

quiet 3-speed control & dimmer

single pole fan control 1.5A (left) **S2-LFSQ-**
single pole dimmer 300W (right)
for use with only one ceiling paddle fan

fully variable control & dimmer

single pole fan control 2.5A (left) **S2-LF-**
single pole dimmer 300W (right)
for use with multiple ceiling paddle fans or exhaust fans

replacement knobs



- standard replacement knobs are available in white, ivory, almond, and light almond

knobs

single pole standard knob **SK-**
split knobs contact customer service