

Eaton S811+N37N3S

Catalog Number: S811+N37N3S

Eaton S811+ soft starter, 65mm 37 A with OPT Inside the Delta

General specifications



Photo is representative

Product Name

Eaton S811+ soft starter

UPC

786685558899

Product Height

11.5 in

Product Weight

7.8 lb

Catalog Number

S811+N37N3S

Product Length/Depth

11 in

Product Width

9 in

Certifications

Contact Manufacturer

Product specifications

Amperage Rating

37A

Special features

30 second ramp or 450% current limit at 50°C, inside-the-delta connection

Type

Severe duty

Frame size

N

Rating

10 kW at 230 V, 18.5 kW at 380-400 V, 18.5 kW at 440 V

Resources

Application notes

S8x1 adjustment - Switching from S801+ to S811+

Catalogs

Solid-State Motor Control, Reduced Voltage Motor Starters, Volume 6, Tab 1

Product Range Catalog Drives Engineering

Multimedia

Soft Starter DS7 up to 32 A

Soft starter DS7 up to 200 A

Soft Starter Product Family Overview

Specifications and datasheets

Eaton Specification Sheet - S811+N37N3S

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton S811+N37N3S

Catalog Number: S811+N37N3S

Eaton S811+ soft starter, 65mm 37 A with OPT Inside the Delta



Photo is representative

General specifications

| | |
|--------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton S811+ soft starter | S811+N37N3S |
| UPC | Product Length/Depth |
| 786685558899 | 11 in |
| Product Height | Product Width |
| 11.5 in | 9 in |
| Product Weight | Certifications |
| 7.8 lb | Contact Manufacturer |

Product specifications

Amperage Rating

37A

Special features

30 second ramp or 450% current limit at 50°C, inside-the-delta connection

Type

Severe duty

Frame size

N

Rating

10 kW at 230 V, 18.5 kW at 380-400 V, 18.5 kW at 440 V

Resources

Application notes

S8x1 adjustment - Switching from S801+ to S811+

Catalogs

Solid-State Motor Control, Reduced Voltage Motor Starters, Volume 6, Tab 1

Product Range Catalog Drives Engineering

Multimedia

Soft Starter DS7 up to 32 A

Soft starter DS7 up to 200 A

Soft Starter Product Family Overview

Specifications and datasheets

Eaton Specification Sheet - S811+N37N3S

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia