## **Specifications**

## Photo is representative





## Eaton S811+N37N3S

Eaton S811+ soft starter, 65mm 37 A with OPT Inside the Delta

General specifications	
PRODUCT NAME	Eaton S811+ soft starter
CATALOG NUMBER	S811+N37N3S
UPC	786685558899
PRODUCT LENGTH/DEPTH	11 in
PRODUCT HEIGHT	11.5 in
PRODUCT WIDTH	9 in
PRODUCT WEIGHT	7.8 lb
CERTIFICATIONS	Contact Manufacturer



Product specifications	S
AMPERAGE RATING	37A
SPECIAL FEATURES	30 second ramp or 450% current limit at 50°C, inside- the-delta connection
ТҮРЕ	Severe duty
FRAME SIZE	N
RATING	10 kW at 230 V, 18.5 kW at 380-400 V, 18.5 kW at 440 V

Resources	
CATALOGS	Solid-State Motor Control, Reduced Voltage Motor Starters, Volume 6, Tab 1
	Product Range Catalog Drives Engineering
	Soft Starter DS7 up to 32 A
MULTIMEDIA	Soft Starter Product Family Overview

	Soft starter DS7 up to 200 A
SPECIFICATIONS AND DATASHEETS	<u>Eaton Specification Sheet -</u> <u>S811+N37N3S</u>
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



**Eaton Corporation plc** 

Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of

Follow us on social media to get the latest product and support information.

their respective owners.







