

# Specifications



Photo is representative



## Eaton S811+T30P3S

Eaton S811+ soft starter, Soft Starter 200MM 304 A Pump control with OPT Inside delta

### General specifications

<b>PRODUCT NAME</b>	Eaton S811+ soft starter
<b>CATALOG NUMBER</b>	S811+T30P3S
<b>UPC</b>	786685559025
<b>PRODUCT LENGTH/DEPTH</b>	19 in
<b>PRODUCT HEIGHT</b>	12.5 in
<b>PRODUCT WIDTH</b>	14.5 in
<b>PRODUCT WEIGHT</b>	45 lb
<b>COMPLIANCES</b>	CE Marked
<b>CERTIFICATIONS</b>	IEC 60947-4-2 EN 60947-4-2 UL Listed CSA Certified CSA Certified for Elevator Duty UL Recognized CSA file No. 3211-06



Powering Business Worldwide

## Product specifications

<b>AMPERAGE RATING</b>	95-304A
<b>SPECIAL FEATURES</b>	30 second ramp or 450% current limit at 50°C, inside-the-delta connection, pump control and extended ramp functions
<b>TYPE</b>	Premium
<b>FRAME SIZE</b>	T
<b>RATING</b>	90 kW at 230 V, 160 kW at 380-400 V, 185 kW at 440 V

## Resources

<b>CATALOGS</b>	<a href="#">Product Range Catalog Drives Engineering</a>
<b>MULTIMEDIA</b>	<a href="#">Soft Starter DS7 up to 32 A</a>
	<a href="#">Soft starter DS7 up to 200 A</a>
	<a href="#">Soft Starter Product Family Overview</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - S811+T30P3S</a>
<b>WARRANTY GUIDES</b>	<a href="#">Selling Policy 25-000 - Distribution and Control Products and Services</a>

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative



## Eaton S811+T30P3S

Eaton S811+ soft starter, Soft Starter 200MM 304 A Pump control with OPT Inside delta

### General specifications

<b>PRODUCT NAME</b>	Eaton S811+ soft starter
<b>CATALOG NUMBER</b>	S811+T30P3S
<b>UPC</b>	786685559025
<b>PRODUCT LENGTH/DEPTH</b>	19 in
<b>PRODUCT HEIGHT</b>	12.5 in
<b>PRODUCT WIDTH</b>	14.5 in
<b>PRODUCT WEIGHT</b>	45 lb
<b>COMPLIANCES</b>	CE Marked
<b>CERTIFICATIONS</b>	IEC 60947-4-2 EN 60947-4-2 UL Listed CSA Certified CSA Certified for Elevator Duty UL Recognized CSA file No. 3211-06



Powering Business Worldwide

## Product specifications

<b>AMPERAGE RATING</b>	95-304A
<b>SPECIAL FEATURES</b>	30 second ramp or 450% current limit at 50°C, inside-the-delta connection, pump control and extended ramp functions
<b>TYPE</b>	Premium
<b>FRAME SIZE</b>	T
<b>RATING</b>	90 kW at 230 V, 160 kW at 380-400 V, 185 kW at 440 V

## Resources

<b>CATALOGS</b>	<a href="#">Product Range Catalog Drives Engineering</a>
<b>MULTIMEDIA</b>	<a href="#">Soft Starter DS7 up to 32 A</a> <a href="#">Soft starter DS7 up to 200 A</a> <a href="#">Soft Starter Product Family Overview</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - S811+T30P3S</a>
<b>WARRANTY GUIDES</b>	<a href="#">Selling Policy 25-000 - Distribution and Control Products and Services</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

