

# Eaton S811+T30P3S

Catalog Number: S811+T30P3S

Eaton S811+ soft starter, Soft Starter 200MM 304 A Pump control with OPT Inside delta



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton S811+ soft starter	S811+T30P3S
<b>UPC</b>	<b>Product Length/Depth</b>
786685559025	19 in
<b>Product Height</b>	<b>Product Width</b>
12.5 in	14.5 in
<b>Product Weight</b>	<b>Compliances</b>
45 lb	CE Marked

## Certifications

IEC 60947-4-2  
EN 60947-4-2  
UL Listed  
CSA Certified  
CSA Certified for Elevator Duty  
UL Recognized  
CSA file No. 3211-06

## Product specifications

### Amperage Rating

95-304A

### Special features

30 second ramp or 450% current limit at 50°C, inside-the-delta connection, pump control and extended ramp functions

### Type

Premium

### Frame size

T

### Rating

90 kW at 230 V, 160 kW at 380-400 V, 185 kW at 440 V

## Resources

### Application notes

[S8x1 adjustment - Switching from S801+ to S811+](#)

### Catalogs

[Product Range Catalog Drives Engineering](#)

### Multimedia

[Soft Starter DS7 up to 32 A](#)

[Soft starter DS7 up to 200 A](#)

[Soft Starter Product Family Overview](#)

### Specifications and datasheets

[Eaton Specification Sheet - S811+T30P3S](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)