



# S8122

F54T5/850/HO/ENV  
54 watt; T5; Fluorescent; 5000K Natural Light; 85 CRI;  
Miniature Bi Pin base

### Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8122

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8122	045923081224	54	T5	Miniature Bi Pin	G5	F54T5/850/HO/ENV	0.63"
MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
45.8"	48"	5000	4650	24000	5000	Natural Light	40
Package Type	CRI	RoHS Compliant					
Sleeve	85	Yes					



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S8122

F54T5/850/HO/ENV  
54 watt; T5; Fluorescent; 5000K Natural Light; 85 CRI;  
Miniature Bi Pin base

### Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8122

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8122	045923081224	54	T5	Miniature Bi Pin	G5	F54T5/850/HO/ENV	0.63"
MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	Kelvin Temp	Color	Pack
45.8"	48"	5000	4650	24000	5000	Natural Light	40
Package Type	CRI	RoHS Compliant					
Sleeve	85	Yes					



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

