



# S8340

CFD26W/4P/841  
26 watt; pin-based Compact Fluorescent; 4100K; 82 CRI;  
G24Q-3 (4-Pin) base

### Features

- Non-integrated Pin Based CFL
- Uses 75% less energy than equivalent incandescent lamps
- TCLP compliant for low mercury
- Meets RoHS standards



S8340

| Item Number    | UPC                 | Watts       | Lamp Shape | Base   | ANSI Base    | Lamp Code     | MOL In Inches  |
|----------------|---------------------|-------------|------------|--------|--------------|---------------|----------------|
| S8340          | 045923083402        | 26          | T4         | G24Q-3 | G24q-3       | CFD26W/4P/841 | 6.5"           |
| Initial Lumens | Average Rated Hours | Kelvin Temp | Color      | Pack   | Package Type | CRI           | RoHS Compliant |
| 1825           | 15000               | 4100        | Cool White | 50     | Hang Box     | 82            | Yes            |
| UL Listed      |                     |             |            |        |              |               |                |
| Yes            |                     |             |            |        |              |               |                |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S8340

CFD26W/4P/841  
26 watt; pin-based Compact Fluorescent; 4100K; 82 CRI;  
G24Q-3 (4-Pin) base

### Features

- Non-integrated Pin Based CFL
- Uses 75% less energy than equivalent incandescent lamps
- TCLP compliant for low mercury
- Meets RoHS standards



S8340

| Item Number    | UPC                 | Watts       | Lamp Shape | Base   | ANSI Base    | Lamp Code     | MOL In Inches  |
|----------------|---------------------|-------------|------------|--------|--------------|---------------|----------------|
| S8340          | 045923083402        | 26          | T4         | G24Q-3 | G24q-3       | CFD26W/4P/841 | 6.5"           |
| Initial Lumens | Average Rated Hours | Kelvin Temp | Color      | Pack   | Package Type | CRI           | RoHS Compliant |
| 1825           | 15000               | 4100        | Cool White | 50     | Hang Box     | 82            | Yes            |
| UL Listed      |                     |             |            |        |              |               |                |
| Yes            |                     |             |            |        |              |               |                |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

