



S8406

F17T8/841/ENV
17 watt; T8; Fluorescent; 4100K Cool White; 85 CRI; Medium Bi Pin base



Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards

S8406

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | MOD In Inches |
|---------------|----------------|----------------|-------------|---------------------|-------------|---------------|---------------|
| S8406 | 045923084065 | 17 | T8 | Medium Bi Pin | G13 | F17T8/841/ENV | 1.00" |
| MOL In Inches | Nominal Length | Initial Lumens | Mean Lumens | Average Rated Hours | Kelvin Temp | Color | Pack |
| 23.78" | 24" | 1450 | 1350 | 20000 | 4100 | Cool White | 30 |
| CRI | RoHS Compliant | | | | | | |
| 85 | Yes | | | | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S8406

F17T8/841/ENV
17 watt; T8; Fluorescent; 4100K Cool White; 85 CRI; Medium Bi Pin base



Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards

S8406

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | MOD In Inches |
|---------------|----------------|----------------|-------------|---------------------|-------------|---------------|---------------|
| S8406 | 045923084065 | 17 | T8 | Medium Bi Pin | G13 | F17T8/841/ENV | 1.00" |
| MOL In Inches | Nominal Length | Initial Lumens | Mean Lumens | Average Rated Hours | Kelvin Temp | Color | Pack |
| 23.78" | 24" | 1450 | 1350 | 20000 | 4100 | Cool White | 30 |
| CRI | RoHS Compliant | | | | | | |
| 85 | Yes | | | | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

