



# S9106

7MR16/LED/40°/5K/12V/DIM  
7 watts; MR16 LED; GU5.3 base; 40° beam spread; 5000K; 12 volts; Dimmable

### Features

- Solid State LED lighting
- High Efficacy
- Long life
- UL approved for totally enclosed fixtures
- Dimmable

### Compatible Dimmers

- Lutron® SELV300 ELV - Use with electronic low-voltage transformer
- Lutron® SLV600P (MLV) - Use with magnetic low-voltage transformer



S9106

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S9106	045923091063	7	MR16	GU5.3	GU5.3	7MR16/LED/40°/5K/12V/DIM	12
Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI
White	1 7/8"	2	560	25000	5000	Natural Light	80
Pack	Beam Spread	RoHS Compliant	UL or ETL Listed				
12/48	40	Yes	Yes				



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S9106

7MR16/LED/40°/5K/12V/DIM  
7 watts; MR16 LED; GU5.3 base; 40° beam spread; 5000K; 12 volts; Dimmable

### Features

- Solid State LED lighting
- High Efficacy
- Long life
- UL approved for totally enclosed fixtures
- Dimmable

### Compatible Dimmers

- Lutron® SELV300 ELV - Use with electronic low-voltage transformer
- Lutron® SLV600P (MLV) - Use with magnetic low-voltage transformer



S9106

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S9106	045923091063	7	MR16	GU5.3	GU5.3	7MR16/LED/40°/5K/12V/DIM	12
Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI
White	1 7/8"	2	560	25000	5000	Natural Light	80
Pack	Beam Spread	RoHS Compliant	UL or ETL Listed				
12/48	40	Yes	Yes				



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

