



S9392

36W/LED/HID/5000K/100-277V
 36 watt - HID Replacement; 5000K; Medium base; 100-277 volts

Features

- High Lumen Omni-directional LED for Industrial / Commercial applications
- Replaces HID, CFL, and Incandescent
- Ballast by-pass - Direct wire only 100V - 277V
- UL approved for totally enclosed fixtures
- Damp location - IP65 rated
- Base up, base down or horizontal operation
- Emits no UV light / Contains no mercury (Hg)
- 5 year limited warranty
- cULus listed

Additional Technical Specifications

- Power Factor >0.9
- Min Starting Temp -20°C
- Max Starting Temp 65°C
- Operating Frequency 50-60Hz
- Working Voltage AC90-305V

Optional accessory: In-line surge protector [80-929](#)



S9392

| Item Number | Product Line | UPC | Input Voltage | Watts | Incandescent Equivalent | Fluorescent Equivalent | HID Equivalent |
|---------------------|--------------|----------------------------|-----------------------|-----------------|-------------------------|--------------------------------|----------------|
| S9392 | Hi-Pro | 045923093920 | 100 - 277 | 36 | 200W | 55W | 150W |
| Base | ANSI Base | Lamp Code | Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens |
| Medium | E26 | 36W/LED/HID/5000K/100-277V | Non-Dimmable | White | 10 3/16" | 3.69" | 4320 |
| Average Rated Hours | Kelvin Temp | Color | CRI | Beam Spread Deg | Pack | Package Type | RoHS Compliant |
| 50000 | 5000 | Natural Light | 80+ | 300 | 12 | Box | Yes |
| UL or ETL Listed | | | | | | Warranty | |
| Yes | | | | | | 5 Year Limited | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S9392

36W/LED/HID/5000K/100-277V
 36 watt - HID Replacement; 5000K; Medium base; 100-277 volts

Features

- High Lumen Omni-directional LED for Industrial / Commercial applications
- Replaces HID, CFL, and Incandescent
- Ballast by-pass - Direct wire only 100V - 277V
- UL approved for totally enclosed fixtures
- Damp location - IP65 rated
- Base up, base down or horizontal operation
- Emits no UV light / Contains no mercury (Hg)
- 5 year limited warranty
- cULus listed

Additional Technical Specifications

- Power Factor >0.9
- Min Starting Temp -20°C
- Max Starting Temp 65°C
- Operating Frequency 50-60Hz
- Working Voltage AC90-305V

Optional accessory: In-line surge protector [80-929](#)



S9392

| Item Number | Product Line | UPC | Input Voltage | Watts | Incandescent Equivalent | Fluorescent Equivalent | HID Equivalent |
|---------------------|--------------|----------------------------|-----------------------|-----------------|-------------------------|--------------------------------|----------------|
| S9392 | Hi-Pro | 045923093920 | 100 - 277 | 36 | 200W | 55W | 150W |
| Base | ANSI Base | Lamp Code | Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens |
| Medium | E26 | 36W/LED/HID/5000K/100-277V | Non-Dimmable | White | 10 3/16" | 3.69" | 4320 |
| Average Rated Hours | Kelvin Temp | Color | CRI | Beam Spread Deg | Pack | Package Type | RoHS Compliant |
| 50000 | 5000 | Natural Light | 80+ | 300 | 12 | Box | Yes |
| UL or ETL Listed | | | | | | Warranty | |
| Yes | | | | | | 5 Year Limited | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

