



S9631

6.5R20/LED/3000K/540L/120V
6.5 watt; LED R20; 3000K; 107' beam spread; Medium base;
120 volts; Dimmable

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9631

| Item Number | Product Line | UPC | Voltage | Watts | Incandescent Equivalent | Power Factor | Lamp Shape |
|---------------------|-----------------------------|----------------------------|--------------------------------|-----------------|-------------------------|---------------|----------------|
| S9631 | DiTTO | 045923096310 | 120 | 6.5 | 50W | 0.90 | R20 |
| Base | ANSI Base | Lamp Code | Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens |
| Medium | E26 | 6.5R20/LED/3000K/540L/120V | Dimmable | Frosted | 3 15/16" | 2.50" | 540 |
| Average Rated Hours | Kelvin Temp | Color | CRI | Beam Spread Deg | Pack | Package Type | RoHS Compliant |
| 25000 | 3000 | Warm White | 80 | 107 | 24/6 | Box | Yes |
| UL or ETL Listed | UL Classification | | Warranty | | | | |
| Yes | cULus - Damp Location Rated | | 3 Year Limited | | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S9631

6.5R20/LED/3000K/540L/120V
6.5 watt; LED R20; 3000K; 107' beam spread; Medium base;
120 volts; Dimmable

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9631

| Item Number | Product Line | UPC | Voltage | Watts | Incandescent Equivalent | Power Factor | Lamp Shape |
|---------------------|-----------------------------|----------------------------|--------------------------------|-----------------|-------------------------|---------------|----------------|
| S9631 | DiTTO | 045923096310 | 120 | 6.5 | 50W | 0.90 | R20 |
| Base | ANSI Base | Lamp Code | Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens |
| Medium | E26 | 6.5R20/LED/3000K/540L/120V | Dimmable | Frosted | 3 15/16" | 2.50" | 540 |
| Average Rated Hours | Kelvin Temp | Color | CRI | Beam Spread Deg | Pack | Package Type | RoHS Compliant |
| 25000 | 3000 | Warm White | 80 | 107 | 24/6 | Box | Yes |
| UL or ETL Listed | UL Classification | | Warranty | | | | |
| Yes | cULus - Damp Location Rated | | 3 Year Limited | | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

