



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

300 East New Hope Road Suite 308  
78613-0000, TX Cedar Park  
Phone: 512-260-0684  
Fax: 512-260-7269



## **SBC3C Split Bolt Conn** *Panduit Corporation*

Catalog Number	SBC3C
Manufacturer	Panduit Corporation
Description	Split Bolt Connector, #8 Awg (Stranded) Conductor Size, #4 Awg (Stranded) Conductor Size, Non-Insulated, Copper Conductor Material, 1.16 In Overall Length, 1 LB/Ea
Weight per unit	1.0 (lbs/each)
Product Category	Large Terminals & Connectors

### **Features**

Material	Copper
media	Yes
Voltage Rating	600 V

### **Material, Color, and Finish**

Finish	Uncoated
--------	----------

### **Descriptions**

Also Known As...	Bug Monkey balls Kearnys Split Bolt Connector
Description	SPLIT BOLT CONN
extra long description	PAN SBC3-C Pan-Lug™ SBC3-C Mech Con
similar brands	Servit®

### **Manufacturer Information**

Brand	PANDUIT
GTIN	00074983627226
UPC	074983627226

### **Taxonomies, Classifications, and Categories**

Category Description	SPLIT BOLTS
Type	Mechanical Split Bolt Connector

### **Packaging**

Carton	1
Package	100
Weight Per each	1



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

300 East New Hope Road Suite 308  
78613-0000, TX Cedar Park  
Phone: 512-260-0684  
Fax: 512-260-7269

---

## Uses, Certifications, and Standards

standard

UL listed to 467 and 486 and CSA certified for use up to 600V &  
Temperature Rated to 90°C

---