



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SC10 Buss SC Fuse Class G Class G

Bussmann Fuses

Catalog Number	SC10
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series Class G Fuse, SC, Fast-Acting, Current Limiting Fuse, 10 A, Rejection Style Fuse, Interrupting Rating Of 100 Ka At 600 Vac and 10 Ka At 170 VDC
Weight per unit	0.1000 (lbs/each)
Product Category	Dual Element

Features

amperage rating	10 Amp
class	G
connection	Ferrule End X Ferrule End
dimensions	1.3100 IN X 0.4100 IN X 0.4100 IN
interrupt rating	100000 Amp (RMS Symmetrical), 10000 Amp (DC)
media	Yes
Voltage Rating	600 Vac, 170 Vdc

Dimensions and Weight

Size	0.41 In Diameter X 1.31 In Length
------	-----------------------------------

Descriptions

Description	BUSS SC FUSE CLASS G CLASS G
extra long description	BUSS SC-10 BUSS SC FUSE CLASS G CLA
Features	Bussmann's SC type fuses are UL Class G and provide fast-acting (1/2-6 A) and time-delay (7-60 A) characteristics for circuit protection need. SC fuses are size rejecting in terms of their overall length thereby aiding in the prevention of overfusing
Long Description	Eaton Bussmann Series Class G fuse, SC, fast-acting, current limiting fuse, 10 A, rejection style fuse, interrupting rating of 100 kA at 600 Vac and 10 kA at 170 Vdc
Product Type	Buss SC Fuse Class G Class G
Special Features	Rejection Style

Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712250108
Manufacturers Part Number	SC-10
UPC	051712250108

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	FUSE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.1

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	RoHS Compliant