



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SC150 1-1/2" Flex Conn D/C Squeeze Type

*Appleton/Oz Gedney*

Catalog Number	SC150
Manufacturer	Appleton/Oz Gedney
Description	Features:2.52IN Dia X 2.09IN Length, 0.71 In Thread Length, Flexible Metal Conduit, Application:Dry Location, Standard:UI 514B, Csa C22.2, Nema FB-1, Size:1.5IN, Connection:Male NPS Thread, Material:Zinc Die Cast
Weight per unit	0.4000 (lbs/each)
Product Category	Liquid Tight Fittings

### Features

angle	Straight
connection	Male NPS Thread
Connector Type	Squeeze
insulation	Non Insulated
Material	Zinc Die Cast

### Material, Color, and Finish

Color	Metallic
Finish	Natural

### Dimensions and Weight

Size	1.5
------	-----

### Descriptions

Description	1-1/2" FLEX CONN D/C SQUEEZE TYPE
extra long description	EGS SC-150 1-1/2 IN SQUEEZE CONN FL
Long Description	Features:2.52IN Dia X 2.09IN Length, 0.71 IN Thread Length, Flexible Metal Conduit, Application:Dry Location, Standard:UL 514B, CSA C22.2, NEMA FB-1, Size:1.5IN, Connection:Male NPS Thread, Material:Zinc Die Cast
Product Type	1-1/2 In Squeeze Conn Flex/Ac
Special Features	2.52 IN Dia X 2.09 IN Length, 0.71 IN Thread Length, Flexible Metal Conduit

### Manufacturer Information

Brand	Appleton
GTIN	00687855201501
Manufacturers Part Number	SC150
UPC	687855201501

### Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	Straight Squeeze Connector



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Trade Size

Trade Size ..... 1.5

## Packaging

Carton ..... 5

Package ..... 50

Weight Per each ..... 0.4

## Uses, Certifications, and Standards

Application ..... Terminates flexible metal conduit to a knockout in a dry location  
box or enclosure

environmental conditions ..... Dry Location

nema rating ..... FB-1

standard ..... UL Standard: 514B; UL Listed: E32539, CSA Standard: C22.2 No.  
18.3, CSA Certified: 208044; NEMA: FB-1