



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SC38 3/8" Flex Conn D/C Squeeze Type

*Appleton/Oz Gedney*

|                  |                                                                                                                                                                                                                       |
|------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | SC38                                                                                                                                                                                                                  |
| Manufacturer     | Appleton/Oz Gedney                                                                                                                                                                                                    |
| Description      | Features:1.06IN Dia X 1.5IN Length, 0.48 In Thread Length, Flexible Metal Conduit, Application:Dry Location, Standard:UL 514B, Csa C22.2, Nema FB-1, Size:0.375IN, Connection:Male NPS Thread, Material:Zinc Die Cast |
| Weight per unit  | 0.0600 (lbs/each)                                                                                                                                                                                                     |
| Product Category | Liquid Tight Fittings                                                                                                                                                                                                 |

### Features

|                |                 |
|----------------|-----------------|
| angle          | Straight        |
| connection     | Male NPS Thread |
| Connector Type | Squeeze         |
| insulation     | Non Insulated   |
| Material       | Zinc Die Cast   |

### Material, Color, and Finish

|        |          |
|--------|----------|
| Color  | Metallic |
| Finish | Natural  |

### Dimensions and Weight

|      |       |
|------|-------|
| Size | 0.375 |
|------|-------|

### Descriptions

|                        |                                                                                                                                                                                                                       |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | 3/8" FLEX CONN D/C SQUEEZE TYPE                                                                                                                                                                                       |
| extra long description | EGS SC-38 3/8 IN SQUEEZE CONN FLEX/                                                                                                                                                                                   |
| Long Description       | Features:1.06IN Dia X 1.5IN Length, 0.48 IN Thread Length, Flexible Metal Conduit, Application:Dry Location, Standard:UL 514B, CSA C22.2, NEMA FB-1, Size:0.375IN, Connection:Male NPS Thread, Material:Zinc Die Cast |
| Product Type           | 3/8 In Squeeze Conn Flex/Ac                                                                                                                                                                                           |
| Special Features       | 1.06 IN Dia X 1.5 IN Length, 0.48 IN Thread Length, Flexible Metal Conduit                                                                                                                                            |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Appleton       |
| GTIN                      | 00687855200382 |
| Manufacturers Part Number | SC-38          |
| UPC                       | 687855200382   |

### Taxonomies, Classifications, and Categories

|                      |                            |
|----------------------|----------------------------|
| Category Description | FLEX & MC FITTINGS         |
| Type                 | Straight Squeeze Connector |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Trade Size

|            |     |
|------------|-----|
| Trade Size | 0.5 |
|------------|-----|

## Packaging

|        |    |
|--------|----|
| Carton | 50 |
|--------|----|

|         |     |
|---------|-----|
| Package | 500 |
|---------|-----|

|                 |      |
|-----------------|------|
| Weight Per each | 0.06 |
|-----------------|------|

## Uses, Certifications, and Standards

|             |                                                                                    |
|-------------|------------------------------------------------------------------------------------|
| Application | Terminates flexible metal conduit to a knockout in a dry location box or enclosure |
|-------------|------------------------------------------------------------------------------------|

|                          |              |
|--------------------------|--------------|
| environmental conditions | Dry Location |
|--------------------------|--------------|

|             |      |
|-------------|------|
| nema rating | FB-1 |
|-------------|------|

|          |                                                                                                       |
|----------|-------------------------------------------------------------------------------------------------------|
| standard | UL Standard: 514B; UL Listed: E32539, CSA Standard: C22.2 No. 18.3, CSA Certified: 208044; NEMA: FB-1 |
|----------|-------------------------------------------------------------------------------------------------------|