

SL



TECHNICAL SPECIFICATIONS:

- :: Westgate's versatile 2-head flood lights with motion sensor and photocell options
- :: Mounts flush on wall or 4" round weatherproof box
- :: Housing: Die-cast aluminum with powder coat finish
- :: Cover type: clear lens
- :: LED: COB technology
- :: Wattage: 20W (10W per head)
- :: Voltage: 90~135V AC 50/60Hz
- :: CRI: 80
- :: Temperature: -4°F~104°F
- :: Power factor: .90~.97
- :: Beam angle: 100°
- :: Suitable for wet locations, IP65

APPLICATIONS:

- :: Ideal for doorway, pathway and alleys
- :: Great for use with optional motion sensors or photocell



MOTION SENSORS



SL-PIR-WH
180°, 200W Max Load,
Outdoor Motion Sensor
(White & Bronze)



SL-PIR-BZ
180°, 200W Max Load,
Outdoor Motion Sensor
(White & Bronze)




SL-HPIR-WH
240°, 500W Max Load
Outdoor Motion Sensor
(White & Bronze)



SL-HPIR-BZ
240°, 500W Max Load
Outdoor Motion Sensor
(White & Bronze)



SL-PC
UL-listed mini
photocell for SL
series security
lights only



LED SECURITY LIGHTS WITH OPTIONAL MOTION SENSOR OR PHOTOCELL

CATALOG NO.	WATTS	LUMENS	COLOR TEMP	REPLACEMENT RANGE
SL-20W-WHT-50K	20W	950LM/HEAD	5000K	70~100 MH
SL-20W-WHT-30K	20W	950LM/HEAD	3000K	70~100 MH
SL-20W-BZ-50K	20W	950LM/HEAD	5000K	70~100 MH
SL-20W-BZ-30K	20W	950LM/HEAD	3000K	70~100 MH
SL-PIR-BZ	120VAC, UL-RCOGNIZED MINIATURE COMPONENT "FOR SL SERIES" 180°, 200W Max Load			
SL-PIR-WH	120VAC, UL-RCOGNIZED MINIATURE COMPONENT "FOR SL SERIES" 180°, 200W Max Load			
SL-HPIR-BZ	OUTDOOR MOTION SENSOR (WHITE & BRONZE)			
SL-HPIR-WH	OUTDOOR MOTION SENSOR (WHITE & BRONZE)			
SL-PC	240°, 500W Max Load, OUTDOOR MOTION SENSOR (WHITE & BRONZE), Incl. WH & BR trims to match security light color			



SL



TECHNICAL SPECIFICATIONS:

- :: Westgate's versatile 2-head flood lights with motion sensor and photocell options
- :: Mounts flush on wall or 4" round weatherproof box
- :: Housing: Die-cast aluminum wqith powder coat finish
- :: Cover type: clear lens
- :: LED: COB technology
- :: Wattage: 20W (10W per head)
- :: Voltage: 90~135V AC 50/60Hz
- :: CRI: 80
- :: Temperature: -4°F~104°F
- :: Power factor: .90~.97
- :: Beam angle: 100°
- :: Suitable for wet locations, IP65

APPLICATIONS:

- :: Ideal for doorway, pathway and alleys
- :: Great for use with optional motion sensors or photocell



MOTION SENSORS



SL-PIR-WH
180°, 200W Max Load,
Outdoor Motion Sensor
(White & Bronze)



SL-PIR-BZ
180°, 200W Max Load,
Outdoor Motion Sensor
(White & Bronze)




SL-HPIR-WH
240°, 500W Max Load
Outdoor Motion Sensor
(White & Bronze)



SL-HPIR-BZ
240°, 500W Max Load
Outdoor Motion Sensor
(White & Bronze)



SL-PC
UL-listed mini
photocell for SL
series security
lights only



LED SECURITY LIGHTS WITH OPTIONAL MOTION SENSOR OR PHOTOCELL

CATALOG NO.	WATTS	LUMENS	COLOR TEMP	REPLACEMENT RANGE
SL-20W-WHT-50K	20W	950LM/HEAD	5000K	70~100 MH
SL-20W-WHT-30K	20W	950LM/HEAD	3000K	70~100 MH
SL-20W-BZ-50K	20W	950LM/HEAD	5000K	70~100 MH
SL-20W-BZ-30K	20W	950LM/HEAD	3000K	70~100 MH
SL-PIR-BZ	120VAC, UL-RCOGNIZED MINIATURE COMPONENT "FOR SL SERIES" 180°, 200W Max Load			
SL-PIR-WH	120VAC, UL-RCOGNIZED MINIATURE COMPONENT "FOR SL SERIES" 180°, 200W Max Load			
SL-HPIR-BZ	OUTDOOR MOTION SENSOR (WHITE & BRONZE)			
SL-HPIR-WH	OUTDOOR MOTION SENSOR (WHITE & BRONZE)			
SL-PC	240°, 500W Max Load, OUTDOOR MOTION SENSOR (WHITE & BRONZE), Incl. WH & BR trims to match security light color			

