



SL600	6"	7.830	.550		
SL500	5"	6.487	.550		
SL400	4"	5.225	.375	.725	8
SL350	3 1/2"	4.675	.375	.685	8
SL300	3"	4.125	.350	.630	8
SL250	2 1/2"	3.450	.350	.500	8
SL200	2"	2.885	.350	.445	11 1/2
SL150	1 1/2"	2.375	.300	.315	11 1/2
SL125	1 1/4"	2.065	.300	.440	11 1/2
SL100	1"	1.715	.260	.265	11 1/2
SL75	3/4"	1.375	.240	.250	14
SL50	1/2"	1.125	.230	.250	14
PART NO.	TRADE SIZE	"A"	"B"	"C"	"D" THDS/INCH