



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

660 Frazier Commerce Dr.
77303-0000, TX Conroe
Phone: 936-788-6850
Fax: 936-788-8283



SMCBL122BKWH 12/2 WG MC Sol BK/WH/GN Steel Armor 250'

Southwire Company

Catalog Number	SMCBL122BKWH
Manufacturer	Southwire Company
Description	Aluminum Armored Conductor, Solid, #12 Awg Conductor Size, PVC Jacket Material, Thermoplastic Nylon Insulation Material, Copper Conductor Material, 600 V, 20 A, Black, White and Green, Blue Jacket Color, 2 Conductors, 250 FT Overall Length, 0.475 In Outside Diameter, +75 °C (Wet) Operating Temperature, 104 LB/MFT
Weight per unit	0.1050 (lbs/each)
Product Category	Alum Armor Copper Conductors

Features

media	Yes
-------	-----

Dimensions and Weight

Length	250
--------	-----

Descriptions

Description	12/2 WG MC SOL BK/WH/GN STEEL ARMOR 250'
extra long description	SWC 55276901 MC12/2SOLTHHN BKWE 12G
Features	Use this Southwire Company 250 ft. Blue 12/2 Armored MC Cable as branch circuit wiring in commercial, industrial, institutional and multi-residential buildings. Vertical cable tray flame tested. Meets UL, NFPA 70 and NEC safety standards.

Manufacturer Information

GTIN	00032886051753
Manufacturers Part Number	57109701
UPC	032886051753

Taxonomies, Classifications, and Categories

Category Description	BX & MC
Type	MC

Availability

minimum qty	250
-------------	-----

Packaging

Carton	250
Weight Per foot	0.105