



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SP182I Smooth Wallplate 1G Toggle 2G Duplex Iv

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | SP182I |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Smooth Wall Plate 1-Gang Toggle 2-Gang Duplex |
| Weight per unit | 0.1418 (lbs/each) |
| Product Category | Wall Plates & Covers |

Features

| | |
|-----------------|------------------------------------|
| cutout | Toggle and Receptacle |
| insulation | Bare |
| Mounting Type | Exposed Screws |
| Number of Gangs | 3 |
| orientation | Vertical |
| Wall Plate Type | Combination, Outlet, Dimmer/Switch |

Dimensions and Weight

| | |
|-----------|------|
| Size | 5" |
| Thickness | 0.07 |

Descriptions

| | |
|------------------------|--|
| Description | SMOOTH WALLPLATE 1G TOGGLE 2G DUPLEX IV |
| extra long description | P&S SP182I SMOOTH WP 1G TOG 2G DUPL |
| Long Description | Smooth Wall Plate 1-Gang Toggle 2-Gang Duplex |
| Product Type | Smooth WP 1G Tog 2G Duplex Iv |
| Special Features | Non-combustible mar-proof material, seven standards colors, individually wrapped |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007188349 |
| Manufacturers Part Number | SP182-I |
| UPC | 785007188349 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type | Wall Plate |

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 150 |
| Weight Per each | 0.1418 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Residential/Commercial |
| Mounting | WALL |
| standard | UL, CSA, CSA, UL514 |