



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SP28W Plastic Wallplate 3G 2 Toggle Duplex W/Out Line WH

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | SP28W |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Plate Plastic 3GANG 2TOGGLE 1DUPLEX Without Line White |
| Weight per unit | 0.1363 (lbs/each) |
| Product Category | Wall Plates & Covers |

Features

| | |
|-----------------|------------------------------------|
| cutout | Toggle and Receptacle |
| insulation | Bare |
| Mounting Type | Exposed Screws |
| Number of Gangs | 3 |
| orientation | Vertical |
| Wall Plate Type | Dimmer/Switch, Outlet, Combination |

Dimensions and Weight

| | |
|-----------|------|
| Size | 5" |
| Thickness | 0.07 |

Descriptions

| | |
|------------------------|--|
| Description | PLASTIC WALLPLATE 3G 2 TOGGLE DUPLEX W/OUT LINE WH |
| extra long description | P&S SP28W PLATE PLST 3G 2TOG/DUP W/ |
| Long Description | Plate Plastic 3gang 2toggle 1duplex Without Line White |
| Product Type | Plate PLST 3G 2TOG/Dup W/Out Line W |
| Special Features | Standard size plastic smooth wall plate |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007680225 |
| Manufacturers Part Number | SP28-W |
| UPC | 785007680225 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type | Wall Plate |

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 150 |
| Weight Per each | 0.1363 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Residential/Commercial |
| Mounting | WALL |
| standard | UL, CSA, CSA, UL514 |