

TYPE 1 ENCLOSURES



Panel Enclosure – Powder Coated

- Designed to enclose electrical and electronic controls, components and instruments which do not require a dust, oil or water tight environment
- Stock inventory sizes from 8x8x4 to 30x36x8-5/8
- Custom sizes and modifications available



SPECIFICATIONS

- Manufactured from code gauge, low carbon steel
- Mounting holes provided
- Hinged
- Coin latch standard
- Back panel sold separately
- Other hardware options available
- Galvanized available

FINISH

- Standard: Gunsmoke Gray Powder Coated
- Optional powder coat colors and custom silkscreen printing available (see pg. 48)

INDUSTRY STANDARDS

- Type 1 - UL 50 and UL 50E: Intended for indoor use primarily to provide a degree of protection against limited amounts of falling dirt.
- RoHS compliant

ACCESSORIES

CATALOG NUMBER	UPC (761515)	SIZE (W"xH"xD")	WGT	BACK PANEL
PE884CLSO	36010	8x8x4	5	SP88-IS
PE10124CLSO	36020	10x12x4	8	SP1012-IS
PE12124CLSO	36030	12x12x4	10	SP1212-IS
PE10106CLSO	36040	10x10x6	8	SP1010-IS
PE10126CLSO	36050	10x12x6	9	SP1012-IS
PE12126CLSO	36060	12x12x6	11	SP1212-IS
PE12166625CLSO	36080	12x16x6.625	17	SP1216-IS
PE16166625CLSO	36090	16x16x6.625	20	1SP1616-IS
PE16206625CLSO	36095	16x20x6.625	23	1SP1620-IS
PE16208625CLSO	36140	16x20x8.625	27	1SP1620-IS
PE20246625CLSO	36100	20x24x6.625	26	1SP2024-IS
PE20248625CLSO	36150	20x24x8.625	38	1SP2024-IS
PE24246625CLSO	36110	24x24x6.625	28	SP2424-IS
PE24248625CLSO	36160	24x24x8.625	42	SP2424-IS
PE24306625CLSO	36120	24x30x6.625	36	SP2430-IS
PE24366625CLSO	36130	24x36x6.625	44	SP2436-IS
PE24368625CLSO	36170	24x36x8.625	50	SP2436-IS
PE30308625CLSO	36180	30x30x8.625	51	SP3030-IS
PE30368625CLSO	36190	30x36x8.625	65	SP3036-IS



Back Panel – White Powder Coated

- Back panel sold separately
- Manufactured from code gauge, low carbon steel
- Galvanized available

