



Made in the USA Since 1946

EMT Couplings Set Screw Type

- For coupling two ends of electrical metallic tubing
- Steel, zinc plated *
- UL rated Concrete Tight when Taped

EMT Couplings - Set Screw (SS)

Cat. #	Size	Unit Ctn	Std Pkg	WT/ 100
SS60US	1/2"	50	250	10
SS61US	3/4"	25	125	15
SS62US	1"	10	50	24
SS63US	1-1/4"	5	25	44
SS64US	1-1/2"	5	25	68
SS65US	2"	-	20	90
SS66US	2-1/2"	-	5	158
SS67US	3"	-	3	217
SS68US	3-1/2"	-	2	250
SS69US	4"	-	2	283

* Fittings 2 1/2" & Larger May Be Steel or Malleable Iron

Dimensional Table

Cat. #	A Length	B Diameter
SS60US	1.75	.937
SS61US	2.13	1.125
SS62US	2.50	1.375
SS63US	3.25	1.687
SS64US	3.75	1.968
SS65US	4.0	2.406
SS66US	4.25	3.220
SS67US	4.50	3.840
SS68US	4.75	4.360
SS69US	5.00	4.860

SPEC-grade





Made in the USA Since 1946

EMT Couplings Set Screw Type

- For coupling two ends of electrical metallic tubing
- Steel, zinc plated *
- UL rated Concrete Tight when Taped

EMT Couplings - Set Screw (SS)

Cat. #	Size	Unit Ctn	Std Pkg	WT/100
SS60US	1/2"	50	250	10
SS61US	3/4"	25	125	15
SS62US	1"	10	50	24
SS63US	1-1/4"	5	25	44
SS64US	1-1/2"	5	25	68
SS65US	2"	-	20	90
SS66US	2-1/2"	-	5	158
SS67US	3"	-	3	217
SS68US	3-1/2"	-	2	250
SS69US	4"	-	2	283

* Fittings 2 1/2" & Larger May Be Steel or Malleable Iron

Dimensional Table

Cat. #	A Length	B Diameter
SS60US	1.75	.937
SS61US	2.13	1.125
SS62US	2.50	1.375
SS63US	3.25	1.687
SS64US	3.75	1.968
SS65US	4.0	2.406
SS66US	4.25	3.220
SS67US	4.50	3.840
SS68US	4.75	4.360
SS69US	5.00	4.860

SPEC-grade

