

# Specifications

Photo is representative

## Eaton SVX050A1-4A1N2

Eaton SVX adjustable frequency drive, 50HP, NEMA Type 1/IP21, 480V, FR7, Three-phase, EMC H, Standard Software, A/N keypad, No brake chopper, Varnished Boards

### General specifications

<b>PRODUCT NAME</b>	Eaton SVX adjustable frequency drive
<b>CATALOG NUMBER</b>	SVX050A1-4A1N2
<b>UPC</b>	782116103911
<b>PRODUCT LENGTH/DEPTH</b>	10.1 in
<b>PRODUCT HEIGHT</b>	24.8 in
<b>PRODUCT WIDTH</b>	9.3 in
<b>PRODUCT WEIGHT</b>	77.2 lb
<b>WARRANTY</b>	2 year
<b>CERTIFICATIONS</b>	IEC 61800-2 EN 61800-3 Level H UL 508C

## Product specifications

<b>BRAKE CHOPPER</b>	No brake chopper
<b>MODIFICATION</b>	Varnished Boards
<b>HORSEPOWER</b>	50 hp
<b>FRAME SIZE</b>	7
<b>KEYPAD</b>	Alphanumeric
<b>INPUT</b>	EMC H Three-phase
<b>RATING</b>	NEMA 1, IP21
<b>SOFTWARE</b>	Standard

## Resources

<b>APPLICATION NOTES</b>	<a href="#">Electromagnetic compatibility (EMC)</a>
<b>CATALOGS</b>	<a href="#">Product Range Catalog Drives Engineering</a> <a href="#">Solid-State Motor Control, Variable Frequency Drives, Volume 6, Tab 2</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - SVX050A1-4A1N2</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

Photo is representative

## Eaton SVX050A1-4A1N2

Eaton SVX adjustable frequency drive, 50HP, NEMA Type 1/IP21, 480V, FR7, Three-phase, EMC H, Standard Software, A/N keypad, No brake chopper, Varnished Boards

### General specifications

<b>PRODUCT NAME</b>	Eaton SVX adjustable frequency drive
<b>CATALOG NUMBER</b>	SVX050A1-4A1N2
<b>UPC</b>	782116103911
<b>PRODUCT LENGTH/DEPTH</b>	10.1 in
<b>PRODUCT HEIGHT</b>	24.8 in
<b>PRODUCT WIDTH</b>	9.3 in
<b>PRODUCT WEIGHT</b>	77.2 lb
<b>WARRANTY</b>	2 year
<b>CERTIFICATIONS</b>	IEC 61800-2 EN 61800-3 Level H UL 508C

## Product specifications

<b>BRAKE CHOPPER</b>	No brake chopper
<b>MODIFICATION</b>	Varnished Boards
<b>HORSEPOWER</b>	50 hp
<b>FRAME SIZE</b>	7
<b>KEYPAD</b>	Alphanumeric
<b>INPUT</b>	EMC H Three-phase
<b>RATING</b>	NEMA 1, IP21
<b>SOFTWARE</b>	Standard

## Resources

<b>APPLICATION NOTES</b>	<a href="#">Electromagnetic compatibility (EMC)</a>
<b>CATALOGS</b>	<a href="#">Product Range Catalog Drives Engineering</a> <a href="#">Solid-State Motor Control, Variable Frequency Drives, Volume 6, Tab 2</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - SVX050A1-4A1N2</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

