



120 X 240 - 16/32  
120 X 240 Primary Volts - 16/32 Secondary Volts - 1Ø  
Buck-Boost Transformer - Single Phase

1083



Catalog #: T113074

**PRODUCT FEATURES**

- UL listed, CSA certified
- UL Type 3R epoxy encapsulated
- Single or Three Phase Applications
- Wall Mounted
- Covered under Acme's 10 year limited warranty

**BENEFITS**

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in KVA

**UL STANDARD**

UL 506

**CSA STANDARD**

C22.2 No 47

**WARRANTY**

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

**GENERAL PRODUCT INFORMATION**

VA:	-
kVA:	1.50
Primary Voltage:	120 X 240
Secondary Voltage:	16/32
Frequency:	60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

**PRODUCT MEASUREMENTS**

Height (In./cm):	11.62 (29.5)
Width (In./cm):	5.50 (14.0)
Depth (In./cm):	5.13 (13.0)

**CONFIGURATION**

Construction Type:	Encapsulated
Mounting Type:	Wall

**PACKAGING**

Ship Weight (Lbs/Kg):	30 (13.6)
-----------------------	-----------

**COMPLIANCES**

UL Standard: UL 506  
UL Listed: File E79947  
CSA Standard: C22.2 No 47  
CSA Listed: LR7357-32  
Warranty: Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)



120 X 240 - 16/32  
120 X 240 Primary Volts - 16/32 Secondary Volts - 1Ø  
Buck-Boost Transformer - Single Phase

1083



Catalog #: T113074

**PRODUCT FEATURES**

- UL listed, CSA certified
- UL Type 3R epoxy encapsulated
- Single or Three Phase Applications
- Wall Mounted
- Covered under Acme's 10 year limited warranty

**BENEFITS**

- Easily configured for numerous applications
- Lower cost solution
- 5-10 times increase in KVA

**UL STANDARD**

UL 506

**CSA STANDARD**

C22.2 No 47

**WARRANTY**

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

**GENERAL PRODUCT INFORMATION**

VA:	-
kVA:	1.50
Primary Voltage:	120 X 240
Secondary Voltage:	16/32
Frequency:	60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

**PRODUCT MEASUREMENTS**

Height (In./cm):	11.62 (29.5)
Width (In./cm):	5.50 (14.0)
Depth (In./cm):	5.13 (13.0)

**CONFIGURATION**

Construction Type:	Encapsulated
Mounting Type:	Wall

**PACKAGING**

Ship Weight (Lbs/Kg):	30 (13.6)
-----------------------	-----------

**COMPLIANCES**

UL Standard: UL 506  
UL Listed: File E79947  
CSA Standard: C22.2 No 47  
CSA Listed: LR7357-32  
Warranty: Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)