



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



T27SA 3/4" Alu FM7 T Condulet *Appleton/Oz Gedney*

| | |
|------------------|--|
| Catalog Number | T27SA |
| Manufacturer | Appleton/Oz Gedney |
| Description | Conduit Outlet Body, Epoxy Powder Coated, 3/4 In Hub Size, 6.25 In Length, 2.63 In Width, 2 In Height, 0.7 LB/Ea |
| Weight per unit | 0.7000 (lbs/each) |
| Product Category | Alum |

Features

| | |
|------------|-------------------------|
| connection | Tapered Female Threaded |
| Form | 7 |
| Material | Aluminum |

Dimensions and Weight

| | |
|--------|-------|
| Length | 6-1/4 |
| Width | 2.63 |

Descriptions

| | |
|------------------------|--|
| Description | 3/4" ALU FM7 T CONDULET |
| extra long description | APP T27SA 3/4 FM7 BODY TYPE T - ALU |
| Special Features | Accurately tapped, tapered threads for tight, rigid joints and excellent ground continuity;Allow connections for branch runs;Completely interchangeable with Crouse-Hinds Form 7 bodies, gaskets and covers;Connect and change direction of conduit runs;Equivalent FM7 and Form 7 units have identical applications and installation dimensions;Fits flush and snug against flat surfaces for more stable installation;Flat back design provides greater cubic content for easier wire pulling and more room for splicing;Hub |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Appleton |
| GTIN | 00781381600989 |
| UPC | 781381600989 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | FORM 7, 8, CONDULETS, COVERS, & GASKETS |
| Type | Type T Conduit Outlet Body |

Packaging

| | |
|-----------------|-----|
| Carton | 5 |
| Package | 25 |
| Weight Per each | 0.7 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

UL 514A, UL 514B, UL File Number E2527, CSA C22.2 No. 18.3,
CSA 065183, NEMA FB-1
