



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TA350K Type Cu/Al Pressure Term 350A Max Brkras *Eaton Corp*

Catalog Number	TA350K
Manufacturer	Eaton Corp
Description	Eaton Molded Case Circuit Breaker Accessory Terminal, Terminal, 400 A, 250-500 Kcmil Cu/Al, Frame J-K, Series C, Pressure Type Line and Load
Weight per unit	0.1200 (lbs/each)
Product Category	Splicing & Terminating Kits

### Features

Current Rating	400 A
dimensions	2.2000 IN X 1.5000 IN X 1.4000 IN
media	Yes

### Descriptions

Description	TYPE CU/AL PRESSURE TERM 350A MAX BRKRAS
extra long description	ETN TA350K CU/AL PRESSURE TERMINAL
Features	Eaton's Electrical Sector under the Eaton brand offers the widest variety of molded case circuit breakers available today. Designed for electrical and machinery OEMs serving a range of industries and applications these proven designs incorporate the latest in innovation with the high reliability that has been our hallmark since the advent of the circuit breaker in the 1920s
Long Description	Eaton molded case circuit breaker accessory terminal, Terminal, 400 A, 250-500 kcmil Cu/Al, Frame J-K, Series C, Pressure type line and load
Product Type	Cu/Al Pressure Terminal 350A Max BRK As

### Manufacturer Information

Brand	Eaton
GTIN	00786679422465
Manufacturers Part Number	TA350K
UPC	786679422465

### Taxonomies, Classifications, and Categories

Category Description	Powerdefense Breakers
Type	Molded case circuit breaker accessory

### Packaging

Carton	1
Weight Per each	0.12



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /  
Institutional Buildings / Structures - Other

standard

UL Listed, Contact Manufacturer