

Eaton's wallbox dimmers, occupancy & vacancy sensors and timers reduce energy usage, improve ambiance and enhance the elegance of a room.

**Products available:**

**Dimmers**



AAL06 DAL06P SAL06P TAL06P1 RI061

**Occupancy & vacancy sensors**



OS106D1 OS310R OS310U OS306U

**Minute & hour timers**




PT18M PT18H

**Colors available:**

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White), C1 (Color Change Kit: A, W, V), C2 (Color Change Kit: LA, W, V), C4 (Color Change Kit: BK, W, V), C5 (Color Change Kit: BK, W, GY).



(Almond) (Brown) (Black) (Gray)



(Lt. Almond) (Ivory) (White)



**C1 Color kit**

A (Almond), W (White), V (Ivory)

**C2 Color kit**

LA (Light Almond), W (White), V (Ivory)



**C4 Color kit**

BK (Black), W (White), V (Ivory)



**C5 Color kit**

BK (Black), W (White), GY (Gray)

For details on where to buy, please contact your local Eaton sales engineer or rep.

Visit our website:

[www.Cooperwiringdevices.com](http://www.Cooperwiringdevices.com)

Electrical Sector  
203 Cooper Circle  
Peachtree City, GA 30269  
United States  
Eaton.com  
Arrowhart.com

Electrical Sector  
Canada Operations  
5925 McLaughlin Road  
Mississauga, Ontario, L5R 1B8  
Canada  
EatonCanada.ca  
Cooperwiringdevices.com

Electrical Sector  
Mexico Operations  
Carr. Tlalnepantla -  
Cuautitlán Km 17.8 s/n  
Col. Villa Jardín esq.  
Cerrada 8 de Mayo  
Cuautitlán, México CP 54800  
México  
Eaton.mx  
Cooperwiringdevices.com

**Eaton**

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
Eaton.com

© 2015 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. PA610001EN  
July 2015

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton's  
Lighting controls line card



Lighting  
control  
you can  
count on



Powering Business Worldwide

# Lighting controls reference

					Wattages											
	Part No.	Cat. Pg. No.	Trimming	Neutral	INC/HAL	LED / CFL	FLR	ELV	MLV	Wiring configuration	Voltage	Preset	Color / Change kits	Rapid Start	Faceplates	
0-10V dimmers	DF10P-	A-30	High-end	—		120V/1200W 277V/1600W	120V/1200W 277V/1600W			3-way	120V/277V	Yes	C1/C2/C4/C5		DCK1-	
	SF10P-	A-31	High-end	—		120V/1200W 277V/1600W	120V/1200W 277V/1600W			3-way	120V/277V	Yes	A/B/BK/GY/LA/V/W			
Phase-cut dimmers	All Load	AAL06-	A-28	High-end/ Low-end	Yes	600W	300W	600W	600W	600W	Multi-location	120V	Yes	C1/C2/C4/C5	Selectable	
		DAL06P-	A-28	Low-end	—	600W	300W	600W	600W	600W	3-way	120V	Yes	C1/C2/C4/C5	Adjustable	DCK1-
		SAL06P-	A-28	Low-end	—	600W	300W	600W	600W	600W	3-way	120V	Yes	A/BK/GY/LA/V/W	Fixed	
		TAL06P1-	A-28	Low-end	—	600W	300W	600W	600W	600W	3-way	120V	Yes	C1/C2/C4/C5	Adjustable	TCK1-
	Smart	AIM10-	A-29	Low-end	—	1000W				1000W	Multi-location	120V	Yes	A/B/BK/GY/LA/V/W/C1/C2		AMC-__-BP
		AF10-	A-29	Low-end	Yes			1000W			Multi-location	120V	Yes	A/B/BK/GY/LA/V/W/C1/C2		AMC-__-BP
		ARD-	A-29	—	—									A/B/BK/GY/LA/V/W/C1/C2		ARC-__-BP
	Decorator	DI10P-	A-30	Low-end	—	1000W				1000W	3-way	120V	Yes	A/B/BK/GY/LA/V/W		
		DF8AP-	A-30	Low-end	—			1000W			3-way	120V	Yes	A/B/BK/GY/LA/V/W		
		DF8AP7-	A-30	Low-end	—			1000W			3-way	277V	Yes	A/B/BK/GY/LA/V/W		
	Slide	SI061-	A-31	Low-end	—	600W					Single pole	120V		A/B/BK/GY/LA/V/W		
		SI06P	—	Low-end	—	600W				600W	3-way	120V	Yes	B/LA/V/W		
		SI10P-	A-31	Low-end	—	1000W				1000W	3-way	120V	Yes	A/B/BK/GY/LA/V/W		
		SF8AP7-	A-31	Low-end	—			1000W			3-way	277V	Yes	A/B/BK/GY/LA/V/W		
	Toggle	TI061-	A-32	—	—	600W					3-way	120V		A/B/BK/LA/V/W		
		TI061L	A-32	—	—	600W					3-way	120V		N/A (Clear)		
		TI3101-	A-32	—	—	1000W					3-way	120V		A/B/BK/LA/V/W		
		TI3101L	A-32	—	—	1000W					3-way	120V		N/A (Clear)		
	Rotary	RI061-	A-33	—	—	600W					Single pole	120V		A/LA/V/W		RKRD-__-BP
		RI06P-	A-33	—	—	600W					3-way	120V	Yes	A/LA/V/W		RKRD-__-BP
		RI06PL-	A-33	—	—	1000W					3-way	120V	Yes	A/LA/V/W		RKRL-__-BP
		RI101-	A-33	—	—	1000W					3-way	120V		A/LA/V/W		RKRD-__-BP
		RDC15-***	A-33	Low-end	—	300W				300W	Single pole	120V		A/LA/V/W		
		RDC25-***	A-33	Low-end	—	300W				300W	Single pole	120V		A/LA/V/W		
Sensor	OS106D1-	A-38	N/A	Yes	600W				600W	Single pole	120V	Yes	A/BK/GY/LA/V/W		SCKD-__BP	
	VS106D1-	A-38	N/A	Yes	600W				600W	Single pole	120V	Yes	A/BK/GY/LA/V/W		SCKD-__BP	
	OS310R-*	A-39	N/A	Yes	600W	600W	600W	600W	600W	3-way	120V		A/BK/GY/LA/V/W		SCKR-__-BP	
	VS310R-*	A-39	N/A	Yes	600W	600W	600W	600W	600W	3-way	120V		A/BK/GY/LA/W		SCKR-__-BP	
	OS310U-*	A-40	N/A	Yes	1000W	1000W	1000W	1000W	1000W	3-way	120V		A/BK/GY/LA/V/W		SCK1-__-BP	
	VS310U-*	A-40	N/A	Yes	1000W	1000W	1000W	1000W	1000W	3-way	120V		A/BK/GY/LA/W		SCK1-__-BP	
	OS306U-	A-41	N/A	—	600W	600W	600W	600W	600W	3-way	120V		A/BK/GY/LA/V/W		N/A	
	VS306U-	A-41	N/A	—	600W	600W	600W	600W	600W	3-way	120V		A/BK/GY/LA/V/W		N/A	
	Timer	PT18M-**	A-42	N/A	—	1800W/15A	1800W/15A	1800W/15A	1800W/15A	1800W/15A	Single pole	120V		A/B/BK/GY/LA/V/W/C1/C2		PT(1-5)MK-__P
		PT18H-**	A-42	N/A	—	1800W/15A	1800W/15A	1800W/15A	1800W/15A	1800W/15A	Single pole	120V		A/B/BK/GY/LA/V/W/C1/C2		PT(1-5)HK-__P

\* Horsepower capable up to 1/6 HP. \*\* Horsepower capable up to 1/4 HP. \*\*\* Combination light/fan control. 1.5A for fan on RDC15 / 2.5A for fan on RDC25.