



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TC2 6" TC Incandescent Housing

Lithonia Lighting - Acuity

Catalog Number	TC2
Manufacturer	Lithonia Lighting - Acuity
Description	The Incandescent 6-Inch Round Non-IC Housing Is Designed For Use In Non-Insulated Areas or Where Insulation Is Spaced At Least 3 Inches From The Housing and Typically Used In New Construction.
Weight per unit	3.7 (lbs/each)
Product Category	Incandescent Recessed Architec

Features

Lamp Type	Incandescent
Material	Steel
Maximum Operating Temperature	25
Number of Lamps	1
Power Source	Hardwired
Shape	Round

Material, Color, and Finish

Color	Unfinished
-------	------------

Dimensions and Weight

Height	7.5
Length	13.125
Width	13.5

Descriptions

Construction	New Construction
Description	6" TC INCANDESCENT HOUSING
extra long description	LITH TC2 6IN Incandescent New Const
Long Description	The incandescent 6-inch round non-IC housing is designed for use in non-insulated areas or where insulation is spaced at least 3 inches from the housing and typically used in new construction.
Product Type	Housing

Manufacturer Information

Brand	JUNO
GTIN	00661209700247
UPC	661209700247

Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
----------------------	---------------------------

Trade Size

aperture size	6 in
---------------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	6
Weight	4
Weight Per each	3.66

Uses, Certifications, and Standards

Application	Residential
environmental conditions	Indoor
Mounting	Recessed
standard	CSA,UL