



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TC44R Remodel LV HSG & TFMR

Lithonia Lighting - Acuity

Catalog Number	TC44R
Manufacturer	Lithonia Lighting - Acuity
Description	The 4-Inch Round Non-Ic, Low Voltage Remodel Housing Is Ideal For Applications Where The Backside Of The Ceiling Is Not Accessible.
Weight per unit	7.0 (lbs/each)
Product Category	Halogen & Quartz Recessed Arch

Features

Lamp Type	Incandescent
Maximum Operating Temperature	25
Number of Lamps	1
Shape	Round

Dimensions and Weight

Height	8
Length	14
Width	8

Descriptions

Construction	Remodel
Description	REMODEL LV HSG & TFMR
extra long description	LITH TC44R 4IN Low Voltage Remodel
Long Description	The 4-inch round non-IC, low voltage remodel housing is ideal for applications where the backside of the ceiling is not accessible.
Product Type	Housing

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00661209002341
Manufacturers Part Number	TC44R
UPC	661209002341

Trade Size

aperture size	4 in
---------------	------

Packaging

Carton	1
Weight	3.5
Weight Per each	7



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Residential
environmental conditions	Indoor
Mounting	Recessed
standard	CSA,cUL