



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## THHN12STGNMINICP THHN 12 STR Green 1000' Mini CP *Southwire Company*

Catalog Number	THHN12STGNMINICP
Manufacturer	Southwire Company
Description	600 Volts. Copper Conductor. Thermoplastic Insulation/Nylon Sheath, Heat, Moisture, Gasoline and Oil Resistant II. Rated Both THHN and THWN. Also Rated MTW and Awm. Simpull Technology For Easier Pulling.
Weight per unit	0.0240 (lbs/ft)
Product Category	THHN-T90-STR (Stranded)

### Features

Conductor Size	12
media	Yes
Number of Conductors	1
Voltage Rating	600

### Material, Color, and Finish

Insulation Material	PVC
Jacket Material	Nylon

### Dimensions and Weight

Length	1000
--------	------

### Descriptions

Description	THHN 12 STR GREEN 1000' MINI CP
extra long description	SWC 58019504 THHN 12 Str Cu Gn 1000
Features	SIMPull THHN copper conductors are primarily used in conduit and cable trays for services, feeders and branch circuits in commercial or industrial applications as specified in the National Electrical Code. Voltage for all applications is 600 volts. SIMpull THHN copper conductors are designed to be installed without application of a pulling lubricant.
Long Description	600 Volts. Copper Conductor. Thermoplastic Insulation/Nylon Sheath, Heat, Moisture, Gasoline and Oil Resistant II. Rated both THHN and THWN. Also rated MTW and AWM. SIMpull Technology for easier pulling.
Product Type	THHN 12 STR Cu GN 1000 Coilpak™
Special Features	No Lube

### Manufacturer Information

Brand	Copper
GTIN	00032886940637
Manufacturers Part Number	58019504
UPC	032886940637



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Type THHN

## Availability

minimum qty 1000

## Packaging

Carton 1000

Weight Per foot 0.024

## Uses, Certifications, and Standards

Application Commerical