



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



THQL2140 Circuit BRK 10KA QL 2P 12 *Industrial Connections &*

Catalog Number	THQL2140
Manufacturer	Industrial Connections &
Description	THQL 2POLE 120/240V 10K Ic 40 Amp
Weight per unit	700.0 (lbs/each)
Product Category	2 Pole Standard Trip Plug-In

Features

amperage rating	40
frame	Q-Line
interrupt rating	10kA@120 Vac / 10kA@120/240 Vac
Load Rating	HACR
Poles	2
trip range	Non-Interchangeable
Trip Type	LI
Voltage Rating	240 V

Descriptions

Description	CIRCUIT BRK 10KA QL 2P 12
extra long description	GE THQL2140 THQL 2POLE 120/240V 10K
Long Description	THQL 2POLE 120/240V 10K IC 40 AMP
Product Type	THQL 2POLE 120/240V 10K Ic 40 Amps
Special Features	Q Line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications in load centers or lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. The THQL2140 breaker features 2 poles, an ampere

Manufacturer Information

Brand	GE
GTIN	00783164012934
Manufacturers Part Number	THQL2140
UPC	783164012934

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
----------------------	---



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	10
Package	1
Weight Per each	700

Uses, Certifications, and Standards

Application	Thermal Magnetic
standard	E11592