PASS & SEYMOUR®

radiant® Paddle Switches 15A, 120/277VAC



Dependable, high-performance solutions brought to you by Legrand.

TM870, TM873, TM874

Now part of the radiant® collection, our paddle switches offer a better fit, form and finish. The smooth paddle action combines with subtle aesthetic improvements to deliver reliable performance. ON-OFF switches conform to NEMA 430-104 requirements for kitchen disposal units. Ideal for residential, multi-dwelling, commercial office and hospitality applications.

Features & Benefits

Easy-access green hex head ground screw.

External screw-pressure-plate back and side wired. Accepts #14–#10AWG solid & stranded wires, Copper-clad aluminum, and copper wire.



TM870LA

Extra-long, through-body strap eliminates floating installations and imperfect applications.

High-impact resistant thermoplastic construction.

- **Part of the radiant® collection.**
- **Smooth paddle action.**
- **Push wire #14 AWG.**
- **Narrow back body leaves more room for wires in the box.**
- **Tri-drive ground, terminal and mounting screws.**
- **ON-OFF switches conform to NEC 430-104 requirements for kitchen disposal units.**
- **NAFTA-Compliant Switches are ideal for use on projects subject to the provisions of the Buy American Act.**

Compliance

cULus Listed, UL20, Conform to NEMA WD-1 and WD-6 UL Listed, File Number E140596, Standard UL20. cULus listed. Standard CSA C22.2 No. 111. Conform to NEMA WD-1 and WD-6.

Technical Information

Performance	
Electrical	
Maximum Working Voltage	277VAC
Maximum Current Interrupting	15A
Maximum Temperature Rise	30°C
Mechanical	
Terminal Identification	Terminal identification in accordance with UL20
Terminal Accommodation	Back and side wire terminals accepts #14–#10AWG solid & stranded wires, Copper-clad aluminum, and copper wire Push wire terminals accommodate #14 AWG
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	UL20 minimum rating



TM873 LA

Materials	
Face	Thermoplastic
Back Body	Thermoplastic
Line Contacts	.031 Brass
Mounting Strap	.042 Zinc-Plated Steel
Tamper-Resistant Shutters	Thermoplastic
Terminal Screws	#8 Tri-Drive Steel (Neutral = Nickel-Plated Steel)
Ground Screw	#8 Hex Tri-Drive Steel; Zinc Coating with Green Chromate
Mounting Screws	Steel plated

Warranty

1 Year

Ordering Information

Single Pole Switches Grounding

Catalog Number	Rating A	Rating VAC	Color	3rd Party Compliance UL20	3rd Party Compliance C22.2 111
TM870I	15	120/277	Ivory	•	•
TM870W	15	120/277	White	•	•
TM870	15	120/277	Brown	•	•
TM870GRY	15	120/277	Gray	•	•
TM870BK	15	120/277	Black	•	•
TM870LA	15	120/277	Light Almond	•	•
TM870NICC10	15	120/277	Nickel	•	•
TM870DBCC10	15	120/277	Dark Bronze	•	•
TM870GCC10	15	120/277	Graphite	•	•

Three-Way Switches Grounding

TM873I	15	120/277	Ivory	•	•
TM873W	15	120/277	White	•	•
TM873	15	120/277	Brown	•	•
TM873GRY	15	120/277	Gray	•	•
TM873BK	15	120/277	Black	•	•
TM873LA	15	120/277	Light Almond	•	•
TM873NICC10	15	120/277	Nickel	•	•
TM873DBCC10	15	120/277	Dark Bronze	•	•
TM873GCC10	15	120/277	Graphite	•	•

Four-Way Switches Grounding

TM874I	15	120/277	Ivory	•	•
TM874W	15	120/277	White	•	•
TM874	15	120/277	Brown	•	•
TM874BK	15	120/277	Black	•	•
TM874LA	15	120/277	Light Almond	•	•
TM874NICC6	15	120/277	Nickel	•	•
TM874DBCC6	15	120/277	Dark Bronze	•	•
TM874GCC6	15	120/277	Graphite	•	•

Vertical Markets

- **Office**
- **Residential**
- **Multiple Dwelling**
- **Hospitality/Lodging**

Also available in the radiant® collection

- **GFCI Receptacles**
- **Standard & Tamper-Resistant Receptacles**
- **Lighting & Fan Controls**
- **Timers**
- **Combination Devices**
- **USB Charging Devices**
- **Night Lights**
- **Screwless Wall Plates**
- **Sensors**
- **Home Automation Controls**

The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca

FOLLOW US

SF20190 June 2025 ©2025 Legrand All Rights Reserved

PASS & SEYMOUR®

radiant® Paddle Switches 15A, 120/277VAC



Dependable, high-performance solutions brought to you by Legrand.

TM870, TM873, TM874

Now part of the radiant® collection, our paddle switches offer a better fit, form and finish. The smooth paddle action combines with subtle aesthetic improvements to deliver reliable performance. ON-OFF switches conform to NEMA 430-104 requirements for kitchen disposal units. Ideal for residential, multi-dwelling, commercial office and hospitality applications.

Features & Benefits

Easy-access green hex head ground screw.

External screw-pressure-plate back and side wired. Accepts #14–#10AWG solid & stranded wires, Copper-clad aluminum, and copper wire.



TM870LA

Extra-long, through-body strap eliminates floating installations and imperfect applications.

High-impact resistant thermoplastic construction.

- **Part of the radiant® collection.**
- **Smooth paddle action.**
- **Push wire #14 AWG.**
- **Narrow back body leaves more room for wires in the box.**
- **Tri-drive ground, terminal and mounting screws.**
- **ON-OFF switches conform to NEC 430-104 requirements for kitchen disposal units.**
- **NAFTA-Compliant Switches are ideal for use on projects subject to the provisions of the Buy American Act.**

Compliance

cULus Listed, UL20, Conform to NEMA WD-1 and WD-6 UL Listed, File Number E140596, Standard UL20. cULus listed. Standard CSA C22.2 No. 111. Conform to NEMA WD-1 and WD-6.

Technical Information

Performance	
Electrical	
Maximum Working Voltage	277VAC
Maximum Current Interrupting	15A
Maximum Temperature Rise	30°C
Mechanical	
Terminal Identification	Terminal identification in accordance with UL20
Terminal Accommodation	Back and side wire terminals accepts #14–#10AWG solid & stranded wires, Copper-clad aluminum, and copper wire Push wire terminals accommodate #14 AWG
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	UL20 minimum rating



TM873 LA

Materials	
Face	Thermoplastic
Back Body	Thermoplastic
Line Contacts	.031 Brass
Mounting Strap	.042 Zinc-Plated Steel
Tamper-Resistant Shutters	Thermoplastic
Terminal Screws	#8 Tri-Drive Steel (Neutral = Nickel-Plated Steel)
Ground Screw	#8 Hex Tri-Drive Steel; Zinc Coating with Green Chromate
Mounting Screws	Steel plated

Warranty

1 Year

Ordering Information

Single Pole Switches Grounding

Catalog Number	Rating A	Rating VAC	Color	3rd Party Compliance UL20	3rd Party Compliance C22.2 111
TM870I	15	120/277	Ivory	•	•
TM870W	15	120/277	White	•	•
TM870	15	120/277	Brown	•	•
TM870GRY	15	120/277	Gray	•	•
TM870BK	15	120/277	Black	•	•
TM870LA	15	120/277	Light Almond	•	•
TM870NICC10	15	120/277	Nickel	•	•
TM870DBCC10	15	120/277	Dark Bronze	•	•
TM870GCC10	15	120/277	Graphite	•	•

Three-Way Switches Grounding

TM873I	15	120/277	Ivory	•	•
TM873W	15	120/277	White	•	•
TM873	15	120/277	Brown	•	•
TM873GRY	15	120/277	Gray	•	•
TM873BK	15	120/277	Black	•	•
TM873LA	15	120/277	Light Almond	•	•
TM873NICC10	15	120/277	Nickel	•	•
TM873DBCC10	15	120/277	Dark Bronze	•	•
TM873GCC10	15	120/277	Graphite	•	•

Four-Way Switches Grounding

TM874I	15	120/277	Ivory	•	•
TM874W	15	120/277	White	•	•
TM874	15	120/277	Brown	•	•
TM874BK	15	120/277	Black	•	•
TM874LA	15	120/277	Light Almond	•	•
TM874NICC6	15	120/277	Nickel	•	•
TM874DBCC6	15	120/277	Dark Bronze	•	•
TM874GCC6	15	120/277	Graphite	•	•

Vertical Markets

- **Office**
- **Residential**
- **Multiple Dwelling**
- **Hospitality/Lodging**

Also available in the radiant® collection

- **GFCI Receptacles**
- **Standard & Tamper-Resistant Receptacles**
- **Lighting & Fan Controls**
- **Timers**
- **Combination Devices**
- **USB Charging Devices**
- **Night Lights**
- **Screwless Wall Plates**
- **Sensors**
- **Home Automation Controls**

The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca

FOLLOW US

SF20190 June 2025 ©2025 Legrand All Rights Reserved