



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TMC8302 3" Cord Grips *Crouse-Hinds*

Catalog Number	TMC8302
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series TMC Cable Gland, Metal-Clad, Teck Corrugated or Interlocked Steel, or Aluminum, Armoured, Aluminum, Outer Sheath: 2.52-3.28", General Purpose, 3" NPT, Armor Range: 2.45-3.02"
Weight per unit	4.4 (lbs/each)
Product Category	BX, MC, Armored Cable Fittings

Features

dimensions	6.3200 IN X 4.8800 IN X 4.8800 IN
Material	Aluminum

Dimensions and Weight

Size	3/4 in
------	--------

Descriptions

Description	3" CORD GRIPS
extra long description	CRS-H TMC8302 3 AL FT MC CAB ARMOR
Features	For use with metal-clad cable, TECK corrugated cable or interlocked steel or aluminum cable, Crouse-Hinds series TMC cable glands provide a means for terminating at junction boxes, control centers, panelboards and enclosures for motor control and electrical distribution equipment. TMC cable glands form a mechanical watertight connection and may installed in Class I, Division 2 locations provided there are no arcing and sparking risks in accordance with NEC501.10B.
Long Description	Eaton Crouse-Hinds series TMC cable gland, Metal-clad, TECK corrugated or interlocked steel, or aluminum, Armoured, Aluminum, Outer sheath: 2.52-3.28", General purpose, 3" NPT, Armor range: 2.45-3.02"
Product Type	3 Al FT MC Cab Armor Od 2.45-3.02
Special Features	Weight 25 Lb per 100

Manufacturer Information

Brand	Eaton
GTIN	00782274414621
Manufacturers Part Number	TMC8302
UPC	782274414621

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cable gland



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	4.4

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	IP56
Temperature Rating	-25 To 60 Deg C