

Specifications



Photo is representative

Eaton TP278

Eaton Crouse-Hinds series Octagon Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), 1-1/2", Steel, (2) 1/2", (2) 3/4", Fixture rated, 15.5 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series octagon outlet box
CATALOG NUMBER	TP278
UPC	786189102789
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	1.5 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.5 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous
----------------------------	------------------------

Product specifications

BOX SIZE	4"
-----------------	----

	Locations
STANDARDS TYPE	NEC/CEC

DEPTH	1-1/2"
CAPACITY	15.5 cubic in
CONDUIT/CABLE	Conduit (no clamps)
SIDE KNOCKOUTS	(2) 1/2 in, (2) 3/4 in
BOTTOM KNOCKOUTS	(3) 1/2 in, (2) 3/4 in
MATERIAL	Steel
SPECIAL FEATURES	Fixture rated

Resources

CATALOGS

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

CERTIFICATION REPORTS

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

SPECIFICATIONS AND DATASHEETS

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP278](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

Reserved.



Specifications



Photo is representative

Eaton TP278

Eaton Crouse-Hinds series Octagon Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), 1-1/2", Steel, (2) 1/2", (2) 3/4", Fixture rated, 15.5 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series octagon outlet box
CATALOG NUMBER	TP278
UPC	786189102789
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	1.5 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.5 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous
----------------------------	------------------------

Product specifications

BOX SIZE	4"
-----------------	----

	Locations
STANDARDS TYPE	NEC/CEC

DEPTH	1-1/2"
CAPACITY	15.5 cubic in
CONDUIT/CABLE	Conduit (no clamps)
SIDE KNOCKOUTS	(2) 1/2 in, (2) 3/4 in
BOTTOM KNOCKOUTS	(3) 1/2 in, (2) 3/4 in
MATERIAL	Steel
SPECIAL FEATURES	Fixture rated

Resources

CATALOGS

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

CERTIFICATION REPORTS

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

SPECIFICATIONS AND DATASHEETS

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP278](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

Reserved.

