



## TAMPER-RESISTANT COMMERCIAL GRADE RECEPTACLES, IVORY, TR20I

TR20I | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Tamper-Resistant Commercial Grade Receptacle, 20A, 125V, Ivory

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

- Dual mechanical shutter system to help prevent insertions of foreign objects.
- High Impact resistant nylon face.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- Backed-out tri-drive steel terminal screws. Side wire only.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Ivory

Type: Receptacles

Features: Tamper-Resistant

Number Of Poles: 2

Number Of Wires: 3

Special Features: Side Wire Only, Tamper-Resistant

Style: Duplex

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes

cULus: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121406

#### DIMENSIONS

Depth (US): .65"

Height (US): 3.28"

Width (US): 1.32"

#### TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: 5-20R

Volts: 125V

Volts (AC): 125

Capacity: Duplex

Grade Type: Commercial

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant





## TAMPER-RESISTANT COMMERCIAL GRADE RECEPTACLES, IVORY, TR20I

TR20I | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Tamper-Resistant Commercial Grade Receptacle, 20A, 125V, Ivory

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

- Dual mechanical shutter system to help prevent insertions of foreign objects.
- High Impact resistant nylon face.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- Backed-out tri-drive steel terminal screws. Side wire only.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Ivory

Type: Receptacles

Features: Tamper-Resistant

Number Of Poles: 2

Number Of Wires: 3

Special Features: Side Wire Only, Tamper-Resistant

Style: Duplex

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes

cULus: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121406

#### DIMENSIONS

Depth (US): .65"

Height (US): 3.28"

Width (US): 1.32"

#### TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: 5-20R

Volts: 125V

Volts (AC): 125

Capacity: Duplex

Grade Type: Commercial

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

