



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR26362W TR Decor Recp 20A 125V S+B Wire WH

Pass & Seymour/Legrand

Catalog Number	TR26362W
Manufacturer	Pass & Seymour/Legrand
Description	Tamper-Resistant Heavy-Duty Decorator Spec Grade Receptacles, Back and Side Wire, 20A, 125V
Weight per unit	0.2267 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
Material	Nylon
media	Yes
Number of Wires	3
Outlet Type	Tamper-Resistant
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

Material, Color, and Finish

Color	White
Finish	Matte

Dimensions and Weight

Height	3.813
Width	.833



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	TR DECOR RECP 20A 125V S+B WIRE WH
extra long description	P&S TR26362W TR DECO RECEP 20A 125V
Long Description	Tamper-Resistant Heavy-Duty Decorator Spec Grade Receptacles, Back and Side Wire, 20A, 125V
Product Type	TR Deco Recep 20A 125V S+B Wire W
Special Features	Dual mechanical shutter system to help prevent insertion of foreign objects. Auto-ground clip assures positive ground. One-piece, brass, triple-wipe power contacts for lasting retention. Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest. Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation. Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring. External screw-

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007277340
Manufacturers Part Number	TR26362-W
UPC	785007277340

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Outlet

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	100
Weight Per each	0.2267

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
standard	CULUS, UL498, cUL CSA
Temperature Rating	-40° - 60° C